

8 Drive Internal U320 HPDB68 Male SCSI Terminated Cable

StarTech ID: *SCSI320INT9*



Keep your U320 SCSI drives running fast and reliable with the StarTech.com SCSI320INT9, an eight-drive LVD/SE terminated internal SCSI cable. Perfect for high-end workstations or servers with U320 SCSI drives, this 68-pin "twist-n-flat" ribbon cable is fully laminated and designed to strengthen signal integrity and offer reduced crosstalk on all pairs. The plastic pull-tabs make it easy to disconnect the cable without damage to the connectors or your drives. Best of all, the cable comes with a built-in LVD/SE terminator so you don't need to purchase a separate terminator, making the SCSI320INT9 a cost-effective, high-speed solution.

Applications and Solutions

- For use in servers and storage subsystems
- High-end workstations
- Ideal when connecting 8 U320 hard drives to a host controller
- Wiring design ensures 100% compatibility with SCSI U320 & U160 Hard Drives

Features

- Each connector includes a label for easy identification
- Meets current SCSI specifications and ensures maximum performance and data integrity
- Orange color twisted pair construction
- Specially designed to improve system airflow and routability

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - IDC 68 pin Half-Pitch Male
- Connector B: 8 - IDC 68 pin Half-Pitch Male
- Color: Brown
- Maximum Cable Length: 19.68 ft [6 m]
- Carton Quantity: 27
- Shipping (Package) Weight: 0.49 lb [0.22 kg]
- Hard Drive: Supports SCSI U320 & 160 Hard Drives
- Number of Hard Drives: 8
- Cable Type: Flat and Twisted
- Connectors: Half Pitch DB68 Male & 8 Half Pitch DB68 Male
- Connector Spacing:
 - System to Device 1: 20" (508mm)
 - System to Device 1: 20" (508mm)
 - Device 1-2: 5" (127mm)
 - Device 3-4: 5" (127mm)
 - Device 3-4: 5" (127mm)
 - Device 4-5: 5" (127mm)
 - Device 5-6: 5" (127mm)
 - Device 6-7: 5" (127mm)
 - Device 7-8: 4"(101.6mm)

