

## 8 Drive Internal U320 HPDB68 Male SCSI Terminated Cable

StarTech ID: SCSI320INT9



Keep your U320 SCSI drives running fast and reliable with the StarTech.com SCSI320INT9, an eight-drive LVD/SE terminated internal SCSI cable. Perfect for high-end workstations or servers with U320 SCSI drives, this 68-pin "twist-n-flat" ribbon cable is fully laminated and designed to strengthen signal integrity and offer reduced crosstalk on all pairs. The plastic pull-tabs make it easy to disconnect the cable without damage to the connectors or your drives. Best of all, the cable comes with a built-in LVD/SE terminator so you don't need to purchase a separate terminator, making the SCSI320INT9 a cost-effective, high-speed solution.

### Applications

- For use in servers and storage subsystems
- High-end workstations
- Ideal when connecting 8 U320 hard drives to a host controller
- Wiring design ensures 100% compatibility with SCSI U320 & U160 Hard Drives

### Features

- Meets current SCSI specifications and ensures maximum performance and data integrity
- Orange color twisted pair construction
- Each connector includes a label for easy identification
- Specially designed to improve system airflow and routability

## Technical Specifications

Warranty	Lifetime
Connector A	1 - HPDB68 SCSI-3 (68 pin; Half-Pitch; IDC68) Male
Connector B	8 - HPDB68 SCSI-3 (68 pin; Half-Pitch; IDC68) Male
Maximum Cable Length	19.7 ft [6 m]
General Specifications	
General Specifications	20" (508mm)
General Specifications	4"(101.6mm)
General Specifications	5" (127mm)
General Specifications	8
General Specifications	Flat and Twisted
General Specifications	Half Pitch DB68 Male & 8 Half Pitch DB68 Male
General Specifications	Supports SCSI U320 & 160 Hard Drives
Color	Brown
Shipping (Package) Weight	0.5 lb [0.2 kg]

## Certifications, Reports and Compatibility

