

4-drive 68-pin Twisted Pair U160 SCSI Internal Cable with Terminator

StarTech ID: SCSI3INT5TWS



Only the best-quality components are used when StarTech.com's expert manufacturing team creates our cabling and this cable is no different. Our 4-drive 68-pin Twisted Pair SCSI3 Internal cable will let you connect up to 4 SCSI3 hard drives, CD-ROM drives, or other internal SCSI peripherals to a host controller. Backed with a lifetime warranty, these cables help StarTech.com maintain our tradition of offering top-notch parts and products for the best price possible.

Technical Specifications

Warranty	Lifetime
Connector A	1 - HPDB68 SCSI-3 (68 pin; Half-Pitch; IDC68) Male
Connector B	4 - HPDB68 SCSI-3 (68 pin; Half-Pitch; IDC68) Male
Maximum Cable Length	19.7 ft [6 m] Device 1-2 = 5"(127mm), Device 2-3 = 5"(127mm), Device 3-4 = 4.5"(114.7mm)
Connector Spacing	System to Device 1 = 20.5" (520.7mm)
Connectors	Half Pitch DB68 Male, Half Pitch DB68 Male x 4
Length	36 inches (914mm)
Color	Red
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	1 - 37 Inch U2W Terminated Internal SCSI Cable

Certifications, Reports and Compatibility

