

8-drive 68-pin Twisted Pair U160 SCSI Internal Cable with Terminator

StarTech ID: SCSI3INT9TWS



If you're looking for quality parts to configure the workstation of your dreams, look no further than StarTech.com's 37-inch 8-Drive Internal SCSI3 Cable. Featuring Half Pitch DB68 Male, Half Pitch DB68 Male x 8 connectors built with only the highest quality components, our cables have the standard lifetime warranty you expect from StarTech.com.

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - IDC 68 pin Half-Pitch Male
- Connector B: 8 - IDC 68 pin Half-Pitch Male
- Color: Blue
- Maximum Cable Length: 19.68 ft [6 m]
- Shipping (Package) Weight: 0.44 lb [0.2 kg]
- Connectors: Half Pitch DB68 Male, Half Pitch DB68 Male x 8
- Length: 64 inches (1626mm)
- Connector Spacing: System to Device 1 = 20"(508mm)
 - : Device 1-2 = 5"(127mm), Device 2-3 = 5", Device 3-4 = 5", Device 4-5 = 5", Device 5-6 = 5", Device 6-7 = 5", Device 7-8 = 4"(101.6mm)

