

## VGA Video Extender Remote Receiver over Cat 5

StarTech ID: ST121R



The ST121R VGA over Cat5 Video Extender Receiver is specifically designed for use as the receiver unit to the StarTech.com [ST1214T](#) 4 Port, and [ST1218T](#) 8 Port VGA over Cat5 UTP Extender transmitter units, allowing you to split and extend a single VGA source to up to four remote displays.

From the transmitter device, the VGA video signal is sent over standard 4 pair Category 5 or better UTP cable to remote monitors, each connected to an ST121R Cat 5 VGA receiver - supporting distances of up to 150 meters (500 feet).

A cost-effective video extension solution, this receiver is ideal for a wide range of environments including airports, bus depots, retail, or any large buildings where VGA video needs to be extended to long connection distances.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications and Solutions

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshow and in auditoriums

## Features

- Extends video cables by up to 500 ft. (150m)
- Pure hardware design, no software or drivers required
- VESA compliant mounting bracket included for mounting onto back of displays, mounts, and walls.
- Uses standard Category 5 straight-wired, twisted-pair, network patch cable for economical and reliable data transmission

## Technical Specifications

- Warranty: 2 Years
- Product Height: 0.81 in [20.55 mm]
- Product Length: 3.31 in [84.16 mm]
- Maximum Cable Length: 500 ft [152.44 m]
- Maximum Analog Resolutions: 1024x768 @ 500ft(150m)
- Output Current: 600mA
- Carton Quantity: 12
- Shipping (Package) Weight: 1.33 lb [0.6 kg]
- Product Weight: 6.04 oz [171 g]
- Product Width: 2.56 in [65.09 mm]

