

2 Port DVI-I Video Splitter - Digital and Analog

StarTech ID: ST122DVI



This DVI splitter lets you share DVI video signals between two displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source, while maintaining high definition display resolutions up to 1080p.

A simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments), the DVI splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

Designed to provide dependable performance, the DVI splitter/signal distribution amplifier is backed by StarTech.com's 2-year warranty and FREE lifetime tech support.

Applications

- Connect DVI enabled projectors, monitors, plasma screens, commercial billboards, and wall display systems
- Ideal for graphic design, classroom use and training seminars
- Great for use in tradeshow, POS, healthcare, airport, train station and bus terminal settings

Features

- Supports resolutions of up to 1600 x 1200 pixels @ 60 Hz
- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion
- Fully compliant with the DVI 1.0 standard established by the DDWG
- Easy setup for a quick connection in minutes

Technical Specifications

Warranty	2 Years
Ports	2
Connector A	1 - DVI (29 pin) Female
Connector B	2 - DVI (29 pin) Female
General Specifications	1 x 24-pin DVI
General Specifications	1 x Power
General Specifications	1.3 lbs (0.62 kg)
General Specifications	1.65 Inches (42 mm)
General Specifications	1600 x 1200 @ 60Hz
General Specifications	2 x 24-pin DVI
General Specifications	2.9 Inches (75 mm)
General Specifications	25 ~ 165 MHz (VGA ~ UXGA)
General Specifications	7.5V DC (1.5A)
General Specifications	7.8 Inches (200 mm)
General Specifications	DVI 1.0
General Specifications	Source to Display: Max of 33ft (10m)
General Specifications	System with a DVI enabled graphics card
Color	Gray
Product Length	7.9 in [20 cm]
Product Width	3 in [7.5 cm]
Product Height	1.7 in [4.2 cm]
Product Weight	21.9 oz [620 g]
Input Voltage	7.5
Input Current	1.5
Shipping (Package) Weight	3 lb [1.4 kg]

Certifications, Reports and Compatibility

