

## 2 Port High Resolution VGA Video Splitter with Audio - 400 MHz

StarTech ID: ST122PROA



This high resolution VGA splitter offers a practical solution for high-res multi-screen presentations, allowing a VGA video signal as well as the corresponding audio to be broadcast from a computer to up to two sets of VGA monitors and speakers simultaneously.

The VGA splitter is ideal for classrooms, tradeshow, in-store displays or any application where high quality video and audio is required, supporting displays with up to 400 MHz of video bandwidth and high resolution applications up to 2048 x 1536.

To help ensure high quality VGA video even at longer distances, the high resolution VGA splitter features a built-in booster circuit that allows monitors to be located up to 210ft away from the host system.

Designed for simplicity and convenience, the VGA splitter offers easy plug and play installation; a completely hardware-based solution, the VGA splitter requires no software operation, saving both time and hassle.

Backed by our 2-year warranty and free lifetime technical support, this 2-port high-resolution VGA splitter lets you get the most out of your video content with quality construction you can depend on.

### Applications

- In-store product merchandising
- Information booths/kiosks
- Trade-shows
- Lecture halls and classrooms
- Airports, bus terminals and train stations

## Features

- Compatible with VGA, SVGA and Multisync monitors
- 400 MHz bandwidth provides brilliant 2048 x 1536 resolution
- DDC, DDC2 & DDC2B compatible (on Video Out port 1)
- Includes DC 7.5V power adapter
- Daisy chainable for almost unlimited expansion
- Uses standard monitor extension cables (StarTech.com coaxial VGA cables recommended for best picture quality)

## Technical Specifications

Warranty	2 Years
Ports	2
Audio	Yes
Connector A	1 - 3.5 mm Mini-Jack (3 Position) Female
Connector A	1 - VGA (15 pin; High Density D-Sub) Female
Connector B	2 - 3.5 mm Mini-Jack (3 Position) Female
Connector B	2 - VGA (15 pin; High Density D-Sub) Female
Maximum Analog Resolutions	2046x1536 @ 60Hz
Bandwidth	400MHz
Color	Gray
Product Length	5.1 in [13 cm]
Product Width	3 in [7.5 cm]
Product Height	2.8 in [7.2 cm]
Product Weight	15.4 oz [437 g]
Power Adapter Included	Yes
Output Voltage	12 DC
Output Current	0.6A
<b>Note</b>	Units made before August 2008 shipped with AC 7.5V 800mA power adapter
Shipping (Package) Weight	2.1 lb [1 kg]
Included in Package	1 - 2 Port VGA Splitter
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

