

## 4 Port VGA Video Splitter - 250 MHz

StarTech ID: ST124LEU



The ST124LEU 4 Port VGA Video Splitter allows a single VGA source to display VGA video onto four monitors simultaneously. Perfect for classrooms, tradeshows, or in-store displays where high quality video on several monitors is needed. The simple plug and play operation makes setup quick and easy so you can be up and running in minutes.

The ST124LEU supports up to 250 MHz of video bandwidth, providing brilliant resolutions up to 1920x1440. A built-in booster circuit lets you situate your displays up to 210 ft away from your source.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications and Solutions

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

## Features

- Supports resolutions up to 1920x1440
- Compatible with VGA, SVGA and Multisync monitors
- Supports Cascading up to 3 levels
- 250MHz video bandwidth
- Supports cable distances up to 210ft

## Technical Specifications

- Warranty: 2 Years
- Bandwidth: 250 MHz
- Product Height: 25.908
- Product Length: 65.024
- Maximum Cable Length: 213.2 ft [65 m]
- Maximum Analog Resolutions: 1920x1440
- Output Current: 500mA
- Carton Quantity: 10
- Shipping (Package) Weight: 2.14 lb [0.97 kg]
- Product Weight: 221
- Product Width: 131.064