

4 Port High Resolution VGA Video Splitter with Audio - 400 MHz

StarTech ID: ST124PROA



This 4-Port High Resolution VGA Video Splitter is an ideal solution for multi-screen presentations that require audio.

The VGA splitter lets you split VGA video and a corresponding audio signal from one computer between four sets of VGA displays and speakers - perfect for classrooms, in-store merchandising, or information kiosks, making sure your presentation stands out in a crowd!

Ensuring high resolution video even at long distances, the splitter features a built-in signal booster that lets you position displays (and speakers) up to 210ft away from the computer.

To provide a high quality viewing experience, the VGA video splitter offers a video bandwidth of 400 MHz with support for high resolution VGA display up to 2048 x 1536.

This high resolution VGA video splitter offers simple plug and play installation, allowing you to deploy your multimedia configuration in minutes.

Applications and Solutions

- Airports, bus terminals and train stations
- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Trade-shows

Features

- 400 MHz bandwidth provides brilliant 2048 x 1536 resolution
- Compatible with VGA, SVGA and Multisync monitors
- Daisy chainable for almost unlimited expansion
- DDC, DDC2 & DDC2B compatible (on Video Out port 1)
- Includes DC 7.5V power adapter
- Uses standard monitor extension cables (StarTech.com coaxial VGA cables recommended for best picture quality)

Technical Specifications

- Warranty: 1 Year warranty
- Color: Gray
- Connector Types: 5 - High Density 15 pin Female
- Connector Types: 5 - Phono 3.5 mm Female
- Product Height: 2.83 in [72 mm]
- Input Current: 0.8
- Input Voltage: 7.5
- Product Length: 5.12 in [130 mm]
- Maximum Analog Resolutions: 2048 x 1536
- Carton Quantity: 12
- Shipping (Package) Weight: 2.59 lb [1.17 kg]
- Product Weight: 23.23 oz [658 g]
- Product Width: 2.95 in [7.5 cm]
- Cable Length: 210 feet (65 meters)
- Dimensions: 5.1 x 2.9 x 1.6 Inches (130 x 75 x 72 mm)
- Input Connectors: Video: 1 x High Density DB15 (Female), Audio: 1 x 3.5mm Audio Jack (Female)
- Output Connectors: Video: 4 x High Density DB15 (Female), Audio: 4 x 3.5mm Audio Jack (Female)
- Power: AC 7.5V 800mA (max)
- Signal Type: XGA, VGA, SVGA, QXGA, UXGA & Multisync displays
- VGA Bandwidth: 400 MHz
- VGA Resolution: 2046 x 1536 @ 60 Hz

CE FC