

## 4 Port High Resolution VGA Video Splitter with Audio - 400 MHz

StarTech ID: ST124PROA



This 4-Port High Resolution VGA Video Splitter is an ideal solution for multi-screen presentations that require audio.

The VGA splitter lets you split VGA video and a corresponding audio signal from one computer between four sets of VGA displays and speakers - perfect for classrooms, in-store merchandising, or information kiosks, making sure your presentation stands out in a crowd!

Ensuring high resolution video even at long distances, the splitter features a built-in signal booster that lets you position displays (and speakers) up to 210ft away from the computer.

To provide a high quality viewing experience, the VGA video splitter offers a video bandwidth of 400 MHz with support for high resolution VGA display up to 2048 x 1536.

This high resolution VGA video splitter offers simple plug and play installation, allowing you to deploy your multimedia configuration in minutes.

### Applications

- In-store product merchandising
- Information booths/kiosks
- Trade-shows
- Lecture halls and classrooms
- Airports, bus terminals and train stations

## Features

- Compatible with VGA, SVGA and Multisync monitors
- 400 MHz bandwidth provides brilliant 2048 x 1536 resolution
- DDC, DDC2 & DDC2B compatible (on Video Out port 1)
- Includes DC 7.5V power adapter
- Daisy chainable for almost unlimited expansion
- Uses standard monitor extension cables (StarTech.com coaxial VGA cables recommended for best picture quality)

## Technical Specifications

Warranty	2 Years
Connector Type(s)	5 - 3.5 mm Mini-Jack (3 Position) Female
Connector Type(s)	5 - VGA (15 pin; High Density D-Sub) Female
Maximum Analog Resolutions	2048x1536
Cable Length	210 feet (65 meters)
Dimensions	5.1 x 2.9 x 1.6 Inches (130 x 75 x 72 mm)
Input Connectors	Video: 1 x High Density DB15 (Female), Audio: 1 x 3.5mm Audio Jack (Female)
Output Connectors	Video: 4 x High Density DB15 (Female), Audio: 4 x 3.5mm Audio Jack (Female)
Power	AC 7.5V 800mA (max)
Signal Type	XGA, VGA, SVGA, QXGA, UXGA & Multisync displays
VGA Bandwidth	400 MHz
VGA Resolution	2046 x 1536 @ 60 Hz
Color	Gray
Product Length	5.1 in [130 mm]
Product Width	3 in [7.5 cm]
Product Height	2.8 in [72 mm]
Product Weight	23.2 oz [658 g]
Input Voltage	7.5
Input Current	0.8
Shipping (Package) Weight	2.6 lb [1.2 kg]

Certifications, Reports and Compatibility

