

## 4 Port VGA and Audio over Cat 5 Video Extender

StarTech ID: ST124UTPEA



The ST124UTPEA VGA Video Extender over Cat 5 with Audio simplifies the implementation of digital signage solutions by allowing a single VGA source and corresponding audio to be broadcast to multiple displays at up to 300m (950ft) away over standard Cat 5 or better UTP cabling.

Consisting of the transmitter unit only, this product requires a single receiver unit per remote display that you are connecting. The VGA extender offers the option of using our [STUTPEALR](#) receiver unit. or the [STUTPRXWLA](#) wall-plate receiver.

For even more versatility, you also have the option to expand the amount of remote displays in your setup by adding the [STUTPEA4X](#) VGA & Audio over Cat 5 Line Splitter to your setup multiplying the number of potential displays by four - allowing your VGA and accompanying audio signal to be broadcast to up to a total 16 displays.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## **Applications and Solutions**

- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard
- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at trade-shows and in auditoriums

## Features

- Deliver VGA video and audio to monitors located up to 300m / 950ft away at 1280x1024 / 720p
- Supports maximum resolutions of up to 1920x1080 / 1080p @ 75m / 250ft
- Can be used with four port line splitters (STUTPEA4X) to run a maximum of 16 displays
- Pure hardware design, no software or drivers required
- Extend using standard Cat 5 or better cabling

## Technical Specifications

- Warranty: 2 Years
- Product Height: 1.61 in [41 mm]
- Humidity: 5~90% RH
- Product Length: 8.66 in [220 mm]
- Operating Temperature: 0°C to 50°C (32°F to 122°F)
- Power Adapter - Amperage: 600mA
- Power Adapter - DC Voltage: 12V DC
- Carton Quantity: 10
- Storage Temperature: -20°C to 70°C (-4°F to 158°F)
- Supported Resolutions: 1920x1200 @ 75m(250ft)

1440x900 @ 150m(500ft)

1024x768 @ 300m(950ft)

- Shipping (Package) Weight: 3.98 lb [1.8 kg]
- Product Weight: 23.3 oz [660 g]
- Product Width: 4.69 in [119 mm]

