

## 4 Port VGA and Audio over Cat 5 Video Extender

StarTech ID: ST124UTPEA



The ST124UTPEA VGA Video Extender over Cat 5 with Audio simplifies the implementation of digital signage solutions by allowing a single VGA source and corresponding audio to be broadcast to multiple displays at up to 300m (950ft) away over standard Cat 5 or better UTP cabling.

Consisting of the transmitter unit only, this product requires a single receiver unit per remote display that you are connecting. The VGA extender offers the option of using our [STUTPEALR](#) receiver unit. or the [STUTPRXWLA](#) wall-plate receiver.

For even more versatility, you also have the option to expand the amount of remote displays in your setup by adding the [STUTPEA4X](#) VGA & Audio over Cat 5 Line Splitter to your setup multiplying the number of potential displays by four - allowing your VGA and accompanying audio signal to be broadcast to up to a total 16 displays.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard
- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at trade-shows and in auditoriums

## Features

- Deliver VGA video and audio to monitors located up to 300m / 950ft away at 1280x1024 / 720p
- Supports maximum resolutions of up to 1920x1080 / 1080p @ 75m / 250ft
- Extend using standard Cat 5 or better cabling
- Can be used with four port line splitters (STUTPEA4X) to run a maximum of 16 displays
- Pure hardware design, no software or drivers required

## Technical Specifications

Warranty	2 Years
Ports	4
Cabling	Cat 5 UTP or better
Audio	Yes
Daisy-Chain	Yes
Local Unit Connectors	2 - VGA (15 pin; High Density D-Sub) Female
Local Unit Connectors	4 - RJ-45 Female
Max Distance	300 m / 950 ft
Supported Resolutions	1920x1200 @ 75m(250ft) 1440x900 @ 150m(500ft) 1024x768 @ 300m(950ft)
Audio Specifications	3.5mm Stereo audio supported
Color	Black
Enclosure Type	Aluminum
Product Length	8.7 in [220 mm]
Product Width	4.7 in [119 mm]
Product Height	1.6 in [41 mm]
Product Weight	23.3 oz [660 g]
Power Adapter Included	Yes
Output Voltage	12 DC
Output Current	0.6A
Operating Temperature	05/11/2012eg;C to 505/11/2012eg;C (325/11/2012eg;F to 1225/11/2012eg;F)
Storage Temperature	-205/11/2012eg;C to 705/11/2012eg;C (-45/11/2012eg;F to 1585/11/2012eg;F)
Humidity	5~90% RH
System and Cable Requirements	One <a href="#">STUTPEALR</a> standalone, or <a href="#">STUTPRXWLA</a> wall-plate receiver unit per display that you are connecting
Shipping (Package) Weight	4 lb [1.8 kg]
Included in Package	1 - 4 Port VGA and Audio Over Cat5 Transmitter
Included in Package	2 - Mounting Brackets
Included in Package	3.5 MM Audio Cable M/M (3 ft)
Included in Package	VGA Cable M/M (3 ft)
Included in Package	1 - 1 Bag (Screws)
Included in Package	1 - Universal Power Adapter (NA/UK/EU)
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

