

8 Port High Resolution VGA Video Splitter - 300 MHz

StarTech ID: ST128PRO



The ST128PRO 8 Port High Resolution VGA Video Splitter - 350 MHz splits a VGA video source signal to 8 monitors or projectors simultaneously - a professional grade solution that is perfect for presentations, classrooms, tradeshows, or in-store displays, where the highest quality video on several monitors is needed.

This High Resolution VGA Splitter supports monitors with up to 350MHz of video bandwidth and display resolutions up to 2048x1536 @80Hz. For added versatility, the VGA splitter features an integrated booster circuit that allows the video signal to be extended up to 210 feet (65 meters), enabling you to situate your displays in the most convenient location based on your application.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.
Male to Female VGA extension cable required (MXT101HQ)

Applications

- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Display travel schedules and alerts in airports, bus terminals and train stations etc.
- Create eye-catching displays in trade-shows and auditoriums
- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Features

- Allows 1 VGA video source to simultaneously display on 8 different monitors
- Supports resolutions up to 2048x1536 @ 80Hz
- High video bandwidth (350 MHz)
- Daisy chainable for almost unlimited expansion
- Maximum VGA cable length of 210ft (65m)
- Uses standard monitor extension cables (See Accessories)
- DDC compatible

Technical Specifications

Warranty	2 Years
Ports	8
Regulatory Approvals	FCC Part 15 Class A, CE Mark
Industry Standards	EDID
Daisy-Chain	Yes
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Male
Connector Type(s)	8 - VGA (15 pin; High Density D-Sub) Female
Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	1920x1440 @ 80 Hz
Bandwidth	(-3db): 300MHz
General Specifications	Male to Female VGA extension cable required (MXT101HQ)
Color	Black
Product Length	7.7 in [196 mm]
Product Width	2.8 in [70 mm]
Product Height	1.6 in [40 mm]
Product Weight	43.2 oz [1225 g]
Power Adapter Included	Yes
Output Voltage	9 DC
Output Current	0.6A
Operating Temperature	55/9/2012eg;C to 405/9/2012eg;C (415/9/2012eg;F to 1045/9/2012eg;F)
Humidity	0~80% RH non-condensing
Shipping (Package) Weight	3 lb [1.4 kg]
Included in Package	1 - 8 Port High Res. Video Splitter
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

