

Mountable 4 Port Rugged Industrial USB Hub

StarTech ID: ST4200USBM



This sturdy, industrial grade USB hub can be wall mounted or installed onto a DIN rail for convenient access to its 4 female USB ports, providing a work area, server room, or industrial area with USB 2.0 connectivity.

With support for Hi-Speed USB 2.0 data transfer rates of up to 480 Mbps, this 4 port USB hub is backwards compatible with USB 1.1 specifications and can be powered through the host USB bus, or self powered using a three wire terminal block connector (7-24V).

Applications and Solutions

- Environments subject to large temperature variances or where physical damage may occur, such as within a factory
- Locations where a USB hub needs to be securely mounted to a surface, such as a wall or under a desk

Features

- Optional external power connector
- Support for multiple mounting methods (Wall/Surface mount and DIN rail)
- High Speed USB 2.0 compliant, supporting transfer rates up to 480 Mbps
- All metal construction
- Includes 2 meter USB host cable

Technical Specifications

- Warranty: 2 Years
- Product Height: 1.04 in [26.3 mm]
- LED Indicators: 1 - Power
- Product Length: 4.51 in [114.5 mm]
- Maximum Data Transfer Rate: 480 Mbps
- MTBF: 193317.8 Hours
- Operating Temperature: 0 to 55 Degrees C
- OS Compatibility: OS independent; No software or drivers required
- Carton Quantity: 50
- Industry Standards: USB 2.0
- Storage Temperature: -20 to 85 Degrees C
- Shipping (Package) Weight: 0.91 lb [0.41 kg]
- Product Weight: 14.47 oz [410 g]
- Product Width: 2.26 in [57.3 mm]

