

## Mountable 4 Port Rugged Industrial USB Hub

StarTech ID: ST4200USBM



This sturdy, industrial grade USB hub can be wall mounted or installed onto a DIN rail for convenient access to its 4 female USB ports, providing a work area, server room, or industrial area with USB 2.0 connectivity.

With support for Hi-Speed USB 2.0 data transfer rates of up to 480 Mbps, this 4 port USB hub is backwards compatible with USB 1.1 specifications and can be powered through the host USB bus, or self powered using a three wire terminal block connector (7-24V).

### Applications

- Locations where a USB hub needs to be securely mounted to a surface, such as a wall or under a desk
- Environments subject to large temperature variances or where physical damage may occur, such as within a factory

### Features

- High Speed USB 2.0 compliant, supporting transfer rates up to 480 Mbps
- Support for multiple mounting methods (Wall/Surface mount and DIN rail)
- All metal construction
- Optional external power connector
- Includes 2 meter USB host cable

Technical Specifications

Warranty	2 Years
Ports	4
Industry Standards	USB 2.0
External Ports	1 - Terminal Block (3 Wire)
External Ports	1 - USB B (4 pin) Female
External Ports	4 - USB A (4 pin) Female
Maximum Data Transfer Rate	480 Mbps
MTBF	193,317.8 Hours
OS Compatibility	OS independent; No software or drivers required
Color	Black
Enclosure Type	Steel
Product Length	4.5 in [114.5 mm]
Product Width	2.3 in [57.3 mm]
Product Height	1 in [26.3 mm]
Product Weight	14.5 oz [410 g]
LED Indicators	1 - Power
Power Adapter Included	No
Input Voltage	7 ~ 24 DC
Operating Temperature	05/11/2012eg;C to 555/11/2012eg;C (325/11/2012eg;F to 1315/11/2012eg;F)
Storage Temperature	-205/11/2012eg;C to 855/11/2012eg;C (-45/11/2012eg;F to 1855/11/2012eg;F)
System and Cable Requirements	Any computer with a USB 2.0 port
Shipping (Package) Weight	0.9 lb [0.4 kg]
Included in Package	1 - USB Cable
Included in Package	1 - DIN Mounting Rails
Included in Package	1 - USB 2.0 Hub
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

