

4 Port Compact Black USB 2.0 Hub

StarTech ID: ST4202USB



This 4 Port USB 2.0 Hub connects to one USB 2.0 port on a Mac or PC computer, adding four USB 2.0 ports - allowing you to maximize the number of high speed USB peripherals connected to your computer. The hub supports cascaded installation with other USB 2.0 hubs, supporting up to 127 USB 2.0 device connections - a scalable solution for connecting multiple USB devices to a single host computer.

The 4 port hub includes a power adapter, but can be powered through USB bus connection to the host computer - allowing you to install the hub as needed without worrying about the availability of a power outlet.

The USB 2.0 hub offers an attractive black casing that suits any operating environment and includes a 3ft USB 2.0 A/B male-male cable, for the connection between the hub and the host computer.

Applications and Solutions

- Charge iPod's or other portable devices that can be recharged through USB 2.0

- Add additional USB 2.0 ports to a computer to connect more devices
- Move USB ports further away from the computer chassis with an external hub
- Make hard to reach USB ports more accessible, by being able to position the hub anywhere the cable will reach

Features

- Compact and light-weight design
- Plug and Play and Hot Swap compatible
- Includes optional external power adapter
- High Speed USB 2.0 compliant, with supported data transfer rates up to 480 Mbps
- Backwards compatible with USB 1.1/1.0 devices

Technical Specifications

- Warranty: 2 Years
- Product Height: 0.79 in [20 mm]
- Input Current: 1000mA
- LED Indicators: 1 - Power
- Product Length: 3.94 in [100 mm]
- Maximum Data Transfer Rate: 480 Mbps
- Operating Temperature: 0 to 70 Degrees °C
- OS Compatibility: OS Independent; No software or drivers required. (For Apple, Mac OS 10.2.4 needed for USB 2.0 speeds)
- Output Current: 2000mA
- Carton Quantity: 30
- Industry Standards: USB 2.0
- Shipping (Package) Weight: 0.66 lb [0.3 kg]
- Product Weight: 10.03 oz [284 g]
- Product Width: 2.36 in [60 mm]

