

3 Port USB 2.0 Hub & 16-in-1 Multi Media Memory Card Reader

StarTech ID: ST4205READ



This 3 Port USB 2.0 Hub offers the combined convenience of a 16-in-1 Multi Media Memory Card Reader, all in one stylish enclosure - helping to conserve valuable desk space while allowing you to simplify your USB connections and add memory/media card accessibility.

The USB Hub/Memory Card Reader supports high speed USB 2.0 data transfer speeds, to ensure flawless USB connectivity and quick data transfers. To simplify installation, the hub/reader offers USB bus powered operation, but includes the optional power adapter (for high load situations).

The USB Hub/Memory Card reader also includes a USB cable, and is backed by StarTech.com's 2-year warranty.

Applications and Solutions

- Connect USB 2.0 peripherals to your desktop computer
- Supports the following card types: CF TYPE I, II; IBM Micro Drive; SM; MS; MS PRO; MS DUO; MS PRO DUO; MS MAGIC GATE; MS PRO MAGIC GATE; MS SELECT FUNCTION; SD; xD; MMC; MINI SD; SM RAM Card

Features

- Supports USB 2.0 transfer rates of 480Mbps and backwards compatible to USB 1.1 specification for connecting older USB devices
- Compact and light weight design produces a small footprint taking up little space and allows you to transport the unit anywhere you take your laptop
- Easily drag and drop files, pictures and music files for editing and storage on your laptop computer

Technical Specifications

- Warranty: 2 Years
- Product Height: 0.31 in [8 mm]
- Product Length: 3.07 in [78 mm]
- OS Compatibility: OS independent; No software or drivers required
- Carton Quantity: 8
- Shipping (Package) Weight: 0.62 lb [0.28 kg]
- Product Weight: 1.98 oz [56 g]
- Product Width: 2.28 in [5.8 cm]
- Memory Media type: CF TYPE I, II
- Memory Media Type: IBM Micro Drive
- Memory Media type: SM, SM RAM CARD
- Memory Media type: MS, MS PRO, MS DUO, MS PRO DUO, MS MAGIC GATE, MS PRO MAGIC GATE, MS SELECT

FUNCTION

- Memory Media type: SD, MINI SD
- Memory Media type: xD
- Memory Media type: MMC
- Maximum Data Transfer Rate: 480Mbps
- Industry Standards: USB 2.0
- Operating Temp: 0°C - 60°C
- Operating Humidity: 0% - 80%

