

## VGA Video Extender over Cat 5 Remote Receiver with Audio

StarTech ID: STUTPEALR



The STUTPEALR VGA Video Extender over Cat 5 Remote Receiver with Audio is the receiver unit utilized by our STUTPEA VGA and Audio over Cat 5 extension series. This convenient video distribution system simplifies the implementation of digital signage solutions by allowing a single VGA source and corresponding audio to be broadcast to multiple displays at up to 300m (950ft) away.

Comprised of one receiver unit per display, and either a [ST124UTPEA](#) 4 port VGA & Audio extender or [ST128UTPEA](#) 8 port VGA & Audio extender unit, the VGA and Audio extension series can transmit a single VGA output and corresponding audio to four or eight displays/receivers over standard Cat 5 or better UTP cable.

For even more versatility, you also have the option to multiply the amount of remote displays in your setup by adding the [STUTPEA4X](#) VGA & Audio over Cat 5 Line Splitter to your setup allowing your VGA and accompanying audio signal to be broadcast to up to a total 16 displays.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard
- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at trade-shows and in auditoriums

## Features

- Send video and audio over Cat5 or better cabling to remote displays
- Monitors can be situated up to 300m / 950ft away at a resolution of 1280x1024 / 720p
- Supports maximum resolutions of up to 1920x1080 / 1080p @ 75m / 250ft
- Choice of using a 4 or 8 port transmitter/extender unit – sold separately
- No software or drivers required
- Adjustable EQ and Gain

**Technical Specifications**

Warranty	2 Years
Ports	1
Cabling	Cat 5 UTP or better
Audio	Yes
Daisy-Chain	No
Remote Unit Connectors	1 - 3.5 mm Mini-Jack (3 Position) Female
Remote Unit Connectors	1 - RJ-45 Female
Remote Unit Connectors	1 - VGA (15 pin; High Density D-Sub) Female
Max Distance	300 m / 950 ft
Supported Resolutions	1920x1200 @ 75m(250ft) 1440x900 @ 150m(500ft) 1024x768 @ 300m(950ft)
Wide Screen Supported	Yes
Color	Black
Enclosure Type	Aluminum
Product Length	5.1 in [130 mm]
Product Width	4.4 in [110.5 mm]
Product Height	1 in [25 mm]
Product Weight	9.5 oz [270 g]
Power Adapter Included	Yes
Output Voltage	12 DC
Output Current	0.6A
Center Tip Polarity	Positive
Operating Temperature	05/9/2012eg;C to 505/9/2012eg;C (325/9/2012eg;F to 1225/9/2012eg;F)
Storage Temperature	-205/9/2012eg;C to 705/9/2012eg;C (-45/9/2012eg;F to 1585/9/2012eg;F)
Humidity	5~90% RH
Shipping (Package) Weight	1.6 lb [0.7 kg]
Included in Package	1 - Long Range UTP Receiver
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

