

VGA Wall Plate Video Extender Receiver over Cat 5 with Audio

StarTech ID: STUTPRXWLA



This CAT5 VGA Extender (Receiver) Audio/Video Wall Plate can be used with StarTech.com's UTPEA VGA with Audio extender system, allowing in-wall connections from a VGA video and audio source to a remote location up to 300m (950ft) away.

Both VGA transmitter and receiver units use a 12V DC terminal block connector behind the unit that offers a more secure and economical installation; using Cat5/Cat6 cable to extend the VGA signal offers a cost-effective solution based on the broad availability of networking cable which is far more flexible than VGA cable, not to mention less expensive.

Unlike some video extension systems, our VGA extender wall plates also allow you to make use of an existing networking cable (Cat5, Cat6) infrastructure, eliminating the need to re-run cable in the event of an upgrade from VGA to another video standard, by simply swapping out the wall plates.

Applications and Solutions

- Ideal for applications in:

Education

Corporate

Digital Signage

Healthcare

Hospitality and Entertainment

Houses of Worship

- Ideal for Pro A/V installers and integrators looking for an easy solution to extend VGA video using Cat5 cabling.

Features

- Compatible with UTPEA series 4 and 8 port VGA video extender (ST124UTPEA and ST128UTPEA). Also works with the wall plate VGA video extender transmitter (STUTPTXWLA)
- Maximum VGA and audio extension distance of 300m/950ft (see Specifications for resolutions supported at various distances)
- Powered by terminal block connection

Technical Specifications

- Warranty: 1 Year warranty
- Color: White
- Connector Types: 1 - High Density DB15 Female
- Connector Types: 1 - RJ45 Female
- Connector Types: 1 - Terminal Block
- Enclosure Type: Steel
- Product Height: 38
- LED Indicators: 1 - Power LED
- Product Length: 105
- Number of Ports: 1
- Output Current: 600 mA
- Output Voltage: 12 DC
- Power Adapter Included: Yes
- Carton Quantity: 10
- Shipping (Package) Weight: 1.41 lb [0.64 kg]
- Product Weight: 136
- Product Width: 42
 - 100m (300ft) / 1600x1200
 - 180m (550ft) / 1280x1024
 - 200m (620ft) / 1024x768
 - 300m (950ft) / 800x600
- Distance / Resolution: 50m (150ft) / 1920x1200

