

2 Port Black PS/2 KVM Switch Kit with Cables

StarTech ID: SV211K



This 2 Port KVM Switch Kit lets you control two computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the KVM switch supports video resolutions of up to 2048 x 1536 and includes 3-in-1 (PS/2 and Video) cables to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, this high quality KVM switch is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Applications

- Perfect for integrating two different enterprise computer systems.
- Useful for call centers, help desks, education environments, home gamers and PC enthusiasts.

Features

- All cables come out of the rear of the switch unlike competitor 3-sided "octopus" designs.
- Hot plug - computers can be added without resetting switches or other connected computers.
- Includes two (2) 6 ft. cables.

Technical Specifications

| | |
|----------------------------|--|
| Warranty | 2 Years |
| Audio | No |
| KVM Ports | 2 |
| PC Interface | PS/2 |
| PC Video Type | VGA |
| Multi-Monitor | No |
| Rack-Mountable | No |
| Cables Included | Yes |
| Daisy-Chain | No |
| Console Interface(s) | 1 - VGA (15 pin; High Density D-Sub) Female |
| Console Interface(s) | 2 - PS/2 (6 pin; Mini-DIN) Female |
| Host Connectors | 2 - VGA (15 pin; High Density D-Sub) Female |
| DVI Support | No |
| IP Control | No |
| Maximum Cable Length | 6 ft [1.8 m] |
| Maximum Analog Resolutions | 1920 x 1440 |
| Auto Scan | 3, 8, 15 & 30 seconds |
| Maximum Number of Users | 1 |
| Color | Black |
| Enclosure Type | Plastic |
| Product Length | 6.3 in [160 mm] |
| Product Width | 2.8 in [70 mm] |
| Product Height | 0.8 in [21 mm] |
| Power Adapter Included | Optional |
| Note | Optional Power Adapter requires 9V DC, 600 mA, center positive |
| Shipping (Package) Weight | 1.6 lb [0.7 kg] |
| Included in Package | 1 - 2 Port PS/2 KVM Switch Kit with Cables |
| Included in Package | 2 - Cables |
| Included in Package | 4 - Rubber Feet |
| Included in Package | 1 - Instruction Manual |

Certifications, Reports and Compatibility

