

2 Port KVM Switch with Audio

StarTech ID: SV211KA



This 2-port PS/2 KVM switch is a reliable and cost-saving solution, allowing users to control multiple computers using only one keyboard, monitor and mouse.

To help eliminate boot-up errors, the switch provides mouse/keyboard emulation and supports both hotkey and push-button switching, to deliver a convenient operating experience.

Providing a robust operating environment, this versatile PS/2-KVM switch supports high quality video at resolutions up to 1920x1440, as well as audio - allowing you to share microphones/speakers among connected computers.

An out-of-the-box solution that includes two high quality 3-in-1 KVM cables, this compact desktop KVM switch features PS/2 and DB15 on the side and rear (respectively), helping eliminate clutter for a more organized workspace.

To save further space, the PS/2 KVM switch doesn't require an external power adapter, and features top-panel LEDs and push-buttons to ensure easy accessibility.

A high quality KVM solution designed for maximum durability and dependability, this 2-port PS/2 KVM switch is backed by our 2-year Warranty and free lifetime technical support.

Features

- Auto-scan mode automatically switches between computers
- Front panel LED's indicate which computer is active
- Hot-key or push button control
- Operating system independent
- Power-free operation
- Small, space saving design
- Supports hot-plugging of PS/2 keyboards or mice
- Supports MS Intellimouse (Pro), Explorer, Optical
- Supports PS/2 connections
- Unique 3-in-1 cables prevent connectors from coming loose

Technical Specifications

- Warranty: 2 Year warranty
- Color: Black
- Connector Types: 2 - 6 DIN Female
- Connector Types: 1 - High Density DB15 Female
- Connector Types: 2 - High Density DB15 Male
- Connector Types: 6 - Phono 3.5 mm Female
- Enclosure Type: Plastic
- Audio Support: Yes
- Cascadable: No
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: PS/2
- KVM IP Control: No
- Number of KVM Ports: 2
- Rack-Mountable: No
- KVM TFT: None
- Product Length: 185
- Maximum Cable Length: 1800
- Maximum Number of Computers: 2
- Maximum Analog Resolutions: 1920 x 1440
- Maximum Number of Users: 1
- Power Consumption: 0.5
- Carton Quantity: 12
- Shipping (Package) Weight: 2.52 lb [1.14 kg]
- Product Width: 85
- Max VGA Resolution: 1920x1440 DDC2B
- Computers Supported: 2
- Console Ports: 1 - (1x HDDB15 Female, 2x6 Pin MiniDin Female, 1x Audio, 1x Mic Jack Female)
- Computer Ports: 2 - (2x HDDB15 Female, 2x Audio, 2x Mic Jacks)
- Auto Scan Interval: 3, 8, 15, 30 seconds
- Cables Included: 2 x 6ft(1.8m) 3-in-1 KVM cables
- : 4 x 6ft(1.8m) Audio cables
- Dimemnsions: 20(H)x85(D)x180(L)mm

- Power: Power free operation - optional 9V DC 500mA adapter not included
- Enclosure: Plastic with metal base

