

## 2 Port KVM Switch with Audio

StarTech ID: SV211KA



This 2-port PS/2 KVM switch is a reliable and cost-saving solution, allowing users to control multiple computers using only one keyboard, monitor and mouse.

To help eliminate boot-up errors, the switch provides mouse/keyboard emulation and supports both hotkey and push-button switching, to deliver a convenient operating experience.

Providing a robust operating environment, this versatile PS/2-KVM switch supports high quality video at resolutions up to 1920x1440, as well as audio - allowing you to share microphones/speakers among connected computers.

An out-of-the-box solution that includes two high quality 3-in-1 KVM cables, this compact desktop KVM switch features PS/2 and DB15 on the side and rear (respectively), helping eliminate clutter for a more organized workspace.

To save further space, the PS/2 KVM switch doesn't require an external power adapter, and features top-panel LEDs and push-buttons to ensure easy accessibility.

A high quality KVM solution designed for maximum durability and dependability, this 2-port PS/2 KVM switch is backed by our 2-year Warranty and free lifetime technical support.

## Features

- Unique 3-in-1 cables prevent connectors from coming loose
- Supports PS/2 connections
- Hot-key or push button control
- Power-free operation
- Small, space saving design
- Auto-scan mode automatically switches between computers
- Supports MS Intellimouse (Pro), Explorer, Optical
- Supports hot-plugging of PS/2 keyboards or mice
- Operating system independent
- Front panel LED's indicate which computer is active

**Technical Specifications**

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	PS/2
Multi-Monitor	No
Rack-Mountable	No
Daisy-Chain	No
DVI Support	No
IP Control	No
Maximum Cable Length	5.9 ft [1.8 m]
Maximum Analog Resolutions	1920 x 1440
Maximum Number of Users	1
General Specifications	1 - (1x HDDB15 Female, 2x6 Pin MiniDin Female, 1x Audio, 1x Mic Jack Female)
General Specifications	1920x1440 DDC2B
General Specifications	2
General Specifications	2 - (2x HDDB15 Female, 2x Audio, 2x Mic Jacks)
General Specifications	2 x 6ft(1.8m) 3-in-1 KVM cables
General Specifications	20(H)x85(D)x180(L)mm
General Specifications	3, 8, 15, 30 seconds
General Specifications	4 x 6ft(1.8m) Audio cables
General Specifications	Plastic with metal base
General Specifications	Power free operation - optional 9V DC 500mA adapter not included
Color	Black
Enclosure Type	Plastic
Product Length	7.3 in [185 mm]
Product Width	3.3 in [85 mm]
Power Consumption	0.5W
Shipping (Package) Weight	2.5 lb [1.1 kg]
Included in Package	1 - 2 Port StarView KVM Switch with Audio
Included in Package	2 - 6ft. 3-in-1 cable set
Included in Package	4 - 6ft. custom audio cable set
Included in Package	1 - Bag of rubber feet
Included in Package	1 - Instructional Manual
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Female

Connector Type(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Connector Type(s)	2 - VGA (15 pin; High Density D-Sub) Male
Connector Type(s)	6 - 3.5 mm Mini-Jack (3 Position) Female

**Certifications, Reports and Compatibility**

