

2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio

StarTech ID: SV211KDVI



The SV211KDVI 2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio provides control of two DVI enabled, USB controlled computers, as well as independent audio/microphone switching for uninterrupted audio when switching between PCs.

This USB+DVI KVM Switch features support for high-resolution digital (1920x1200) and analog (2048x1536) video, plus an integrated USB 2.0 hub that allows you to share 2 high-speed USB devices between computers.

Compatible with Mac, Linux and Windows® based computers, this compact DVI KVM is a great space-saving solution for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production and more.

A complete, out-of-the-box solution, this DVI KVM Switch includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate cable clutter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications and Solutions

- Ideal for conserving space when working with multiple desktops, workstations and servers
- Home/SOHO/multimedia environment dual system control for single user workstations
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required
- Applicable for call centers, help desks, education environments, home gamers, and PC enthusiasts

Features

- Supports resolutions up to 1920x1200(digital) and 2048x1536(analog)
- Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers
- Compatible with all USB supported Operating Systems
- Compact design saves space
- Computer selection by push button, keyboard hotkeys and Switching Software (for Windows/Mac)
- Hot Pluggable - add or remove computers without having to power down
- LED indicators for easy status monitoring
- USB 2.0/1.1 specification compliant
- HDCP Compliant

Technical Specifications

- Warranty: 2 Years
- Product Height: 1.06 in [27 mm]
- Humidity: 0~90% RH
- Input Current: 0.4A
- LED Indicators: 1 - Power/Computer Selection Indicator
- Product Length: 6.06 in [154 mm]
- Maximum Number of Computers: 2
- Maximum Digital Resolutions: 1920x1200
- Maximum Analog Resolutions: 2048x1536
- Maximum Number of Users: 1
- Operating Temperature: 0°C to 40°C (32°F to 104°F)
- Output Current: 2A
- Carton Quantity: 12
- Storage Temperature: -20°C to 60°C (-4°F to 140°F)
- Shipping (Package) Weight: 2.76 lb [1.25 kg]
- Product Width: 2.58 in [65.5 mm]

