

## 2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio

StarTech ID: SV211KDVI



The SV211KDVI 2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio provides control of two DVI enabled, USB controlled computers, as well as independent audio/microphone switching for uninterrupted audio when switching between PCs.

This USB+DVI KVM Switch features support for high-resolution digital (1920x1200) and analog (2048x1536) video, plus an integrated USB 2.0 hub that allows you to share 2 high-speed USB devices between computers.

Compatible with Mac, Linux and Windows® based computers, this compact DVI KVM is a great space-saving solution for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production and more.

A complete, out-of-the-box solution, this DVI KVM Switch includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate cable clutter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Ideal for conserving space when working with multiple desktops, workstations and servers
- Home/SOHO/multimedia environment dual system control for single user workstations
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required
- Applicable for call centers, help desks, education environments, home gamers, and PC enthusiasts

## Features

- Supports resolutions up to 1920x1200(digital) and 2048x1536(analog)
- Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers
- Compatible with all USB supported Operating Systems
- Compact design saves space
- Computer selection by push button, keyboard hotkeys and Switching Software (for Windows/Mac)
- Hot Pluggable - add or remove computers without having to power down
- LED indicators for easy status monitoring
- USB 2.0/1.1 specification compliant
- HDCP Compliant

**Technical Specifications**

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No
Console Interface(s)	1 - DVH (29 pin) Female
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	2 - DVH (29 pin) Female
Host Connectors	2 - USB B (4 pin) Female
DVI Support	Yes
IP Control	No
Maximum Analog Resolutions	2048x1536
Maximum Digital Resolutions	1920x1200
Maximum Number of Users	1
Color	White
Enclosure Type	Plastic
Product Length	6.1 in [154 mm]
Product Width	2.6 in [65.5 mm]
Product Height	1.1 in [27 mm]
Product Weight	5.6 oz [160 g]
LED Indicators	1 - Power/Computer Selection Indicator
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N
Operating Temperature	05/8/2012eg;C to 405/8/2012eg;C (325/8/2012eg;F to 1045/8/2012eg;F)

Storage Temperature	-205/8/2012eg;C to 605/8/2012eg;C (-45/8/2012eg;F to 1405/8/2012eg;F)
Humidity	0~90% RH
Shipping (Package) Weight	2.8 lb [1.3 kg]
Included in Package	1 - 2 Port DVI USB KVM
Included in Package	2 - 4 ft. DVI/Audio&Mic combo cables
Included in Package	2 - 4 ft. USB cables
Included in Package	1 - Power Adapter
Included in Package	1 - Software CD

**Certifications, Reports and Compatibility**

