

2 Port Black USB KVM Switch Kit with Audio and Cables

StarTech ID: SV211KUSB



The SV211KUSB 2 Port USB KVM Switch Kit with Audio and Cables lets you control two USB-enabled computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the USB KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the USB KVM switch supports video resolutions of up to 2048 x 1536 as well as audio switching. The USB KVM switch includes two 4ft 2-in-1 VGA and USB Host Cables, providing everything needed for quick installation to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Control 2 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Applicable for call centers, help desks, education environments, home gamers, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice
- Dual system control for single user workstations, increasing user productivity in the office

Features

- Cables (4 ft.) included
- Maximum resolution: 2048 x 1536
- Switching type: Hotkey, push-button
- Includes audio support for a complete switching solution
- Small footprint design
- USB Powered - No external adapter required

Technical Specifications

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	2 - USB Mini (4 pin) Female
Host Connectors	2 - VGA (15 pin; High Density D-Sub) Female
IP Control	No
Maximum Analog Resolutions	2048x1536 @60Hz
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
Color	Black
Enclosure Type	Plastic
Cable Length	4 x 4ft 2-in-1 VGA and USB Host Cables 4 x 4ft 2-in-1 Audio and Mic Cables
Product Width	3.8 in [96 mm]
Product Height	0.8 in [20 mm]
Product Depth	2.4 in [60 mm]
Product Weight	7.1 oz [200 g]
Power Adapter Included	Self Powered
Shipping (Package) Weight	1.7 lb [0.8 kg]
Included in Package	1 - 2 Port KVM Switch
Included in Package	2 - 4ft. Audio Cable (3.5mm speaker/mic)
Included in Package	2 - 4ft. VGA USB KVM Cable
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

