

2 Port USB DVI Cable KVM Switch with Audio

StarTech ID: SV215MICDVIA



The SV215MICDVIA 2 Port USB DVI Cable KVM Switch with Audio allows you to control 2 computers from a single KVM (Keyboard, Video, Mouse) peripheral set, and supports resolutions up to 1920x1200.

This cable-style KVM switch includes all of the cables and connections required, for a complete KVM solution. Plus, the switch features independent audio/mic switching to ensure uninterrupted sound, even when switching between computers.

This broadly compatible USB KVM switch can be connected to Mac, Linux or PC-based computers, making it a convenient solution for most operating environments. Plus, because of its space-saving “KVM-on-a-cable” design, no desk space is required for installation – an ideal choice for most applications, including SOHO (small or home offices), gaming, multimedia production workstations and more.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Control multiple desktops, workstations or servers that require full multi-media support
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required
- Sharing computers and attached peripherals in the home/SOHO/multimedia environment
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice and allows remote access

Features

- Micro cable KVM design with all necessary cables included
- Operating System independent - No software or driver required
- Includes Remote Selector switch and supports hot-key computer selection
- Supports resolutions up to 1920x1200
- Hot Plug - add or remove computers without reboot
- LED indicators for easy status monitoring
- USB 2.0/1.1 specification compliant
- HDCP Compliant

Technical Specifications

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No
Console Interface(s)	1 - DVI-D (19 pin) Male
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	2 - DVI-D (19 pin) Male
Host Connectors	4 - 3.5 mm Mini-Jack (3 Position) Male
Host Connectors	4 - USB A (4 pin) Male
DVI Support	Yes - Single Link
IP Control	No
Maximum Analog Resolutions	1920x1200
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
Color	Black
Enclosure Type	Plastic
Product Weight	21.9 oz [620 g]
Operating Temperature	05/8/2012eg;C to 505/8/2012eg;C (325/8/2012eg;F to 1225/8/2012eg;F)
Storage Temperature	-205/8/2012eg;C to 605/8/2012eg;C (-45/8/2012eg;F to 1405/8/2012eg;F)
Humidity	0~80% RH,
Note	One host cable is 47 inches long, the other is 24 inches. Remote selector is 70 inches long
Shipping (Package) Weight	1.6 lb [0.7 kg]
Included in Package	1 - 2 Port Integrated KVM
Included in Package	1 - Remote Selector
Included in Package	1 - Manual

Certifications, Reports and Compatibility

