

2 Port DVI PS/2 KVM Switch

StarTech ID: SV221DVI



This 2 port DVI KVM Switch (PS/2) offers crystal clear digital images, allowing you to share a flat panel monitor, PS/2 keyboard and PS/2 mouse between two computers.

Designed specifically for DVI flat panel displays, the DVI KVM switch preserves the integrity of digital images ensuring distortion and signal loss is minimized.

A convenient addition to any work environment, the DVI KVM switch supports both hotkey and push-button control and features auto-scanning to simplify monitoring connected computers.

This compact DVI KVM switch offers a cost-effective solution for desktop KVM control, with cable entry situated at the rear of the switch - saving valuable workspace while minimizing cable clutter.

Designed to ensure dependability and long-lasting performance, the 2 port DVI KVM switch is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Applications and Solutions

- Enables users to control 2 computers from 1 Keyboard, Mouse and Flat Panel LCD monitor
- Ideal for environments using desktops, workstations and servers with Flat Panel LCD monitor
- Switches instantly between two PCs

Features

- DVI-I interface technology supports both digital and analog video signal transmission
- All cables are connected to the rear for a more secure and neat connection
- Supports PS/2 keyboards and mouse including M/S IntelliMouse (Pro), Explorer and Optical mice
- Keyboard and mouse allow for hot plugging without having to turn either the KVM or the PC off
- Operating system independent, compatible with all operating systems
- Front panel LED`s indicate which computer is active
- Supports high digital resolution of up to 1280x1024 and analog resolution of up to 1920x1440
- Power-free operation draws power from your computer's PS/2 port and requires no power adapters
- Buzzer sound for port switching confirmation
- HDCP Compliant

Technical Specifications

- Warranty: 2 Years
- Product Height: 1.77 in [45 mm]
- Product Length: 3.39 in [86 mm]
- Maximum Number of Computers: 2
- Maximum Digital Resolutions: 1280 x 1024
- Maximum Analog Resolutions: Analog 1920 x 1440
- Maximum Analog Resolutions: This product is not intended for use with Widescreen displays
- Maximum Number of Users: 1
- Carton Quantity: 10
- Shipping (Package) Weight: 1.7 lb [0.77 kg]
- Product Weight: 18.36 oz [520 g]
- Product Width: 5.51 in [140 mm]
- PC Connectors:
 - Keyboard: 2 x PS/2 6-pin Mini Din (female)
 - Mouse: 2 x PS/2 6-pin Mini Din (female)
 - DVI: 2 x DVI-I Dual Link (female)
- Console Connector:
 - Keyboard: 1 x PS/2 6-pin Mini Din (female)
 - Mouse: 1 x PS/2 6-pin Mini Din (female)
 - DVI: 1 x DVI-I Dual Link (female)
- Port Selection: Push Button and Hot Keys
- Power: PS/2 interface & 9V 500mA Adapter (optional)
- Operating Temperature: 00C ~ 400C
- LED Indicator: Port Status (Numerical display)
- Dimensions:
 - Length: 3.3 Inches (86 mm)
 - Width: 5.1 Inches (140 mm)
 - Height: 1.75 Inches (45 mm)
- Weight: 1.14 Lbs (520 Grams)

