

2 Port DVI PS/2 KVM Switch

StarTech ID: SV221DVI



This 2 port DVI KVM Switch (PS/2) offers crystal clear digital images, allowing you to share a flat panel monitor, PS/2 keyboard and PS/2 mouse between two computers.

Designed specifically for DVI flat panel displays, the DVI KVM switch preserves the integrity of digital images ensuring distortion and signal loss is minimized.

A convenient addition to any work environment, the DVI KVM switch supports both hotkey and push-button control and features auto-scanning to simplify monitoring connected computers.

This compact DVI KVM switch offers a cost-effective solution for desktop KVM control, with cable entry situated at the rear of the switch - saving valuable workspace while minimizing cable clutter.

Designed to ensure dependability and long-lasting performance, the 2 port DVI KVM switch is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Applications

- Enables users to control 2 computers from 1 Keyboard, Mouse and Flat Panel LCD monitor
- Ideal for environments using desktops, workstations and servers with Flat Panel LCD monitor
- Switches instantly between two PCs

Features

- DVI-I interface technology supports both digital and analog video signal transmission
- All cables are connected to the rear for a more secure and neat connection
- Supports PS/2 keyboards and mouse including M/S IntelliMouse (Pro), Explorer and Optical mice
- Keyboard and mouse allow for hot plugging without having to turn either the KVM or the PC off
- Operating system independent, compatible with all operating systems
- Front panel LED`s indicate which computer is active
- Supports high digital resolution of up to 1280x1024 and analog resolution of up to 1920x1440
- Power-free operation draws power from your computer's PS/2 port and requires no power adapters
- Buzzer sound for port switching confirmation
- HDCP Compliant

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	DVI
Multi-Monitor	No
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No
Console Interface(s)	1 - DVH (29 pin) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	2 - DVH (29 pin) Female
Host Connectors	4 - PS/2 (6 pin; Mini-DIN) Female
DVI Support	Yes
IP Control	No
Maximum Analog Resolutions	1920 x 1440
Maximum Digital Resolutions	1280 x 1024
Maximum Number of Users	1
General Specifications	
General Specifications	0 ⁰ C ~ 40 ⁰ C
General Specifications	1.14 Lbs (520 Grams)
General Specifications	DVI: 1 x DVH Dual Link (female)
General Specifications	DVI: 2 x DVH Dual Link (female)
General Specifications	Height: 1.75 Inches (45 mm)
General Specifications	Keyboard: 1 x PS/2 6-pin Mini Din (female)
General Specifications	Keyboard: 2 x PS/2 6-pin Mini Din (female)
General Specifications	Length: 3.3 Inches (86 mm)
General Specifications	Mouse: 1 x PS/2 6-pin Mini Din (female)
General Specifications	Mouse: 2 x PS/2 6-pin Mini Din (female)
General Specifications	Port Status (Numerical display)
General Specifications	PS/2 interface & 9V 500mA Adapter (optional)
General Specifications	Push Button and Hot Keys
General Specifications	Width: 5.1 Inches (140 mm)
Color	Black

Enclosure Type	Steel
Product Length	3.4 in [86 mm]
Product Width	5.5 in [140 mm]
Product Height	1.8 in [45 mm]
Product Weight	18.4 oz [520 g]
Note	This product is not intended for use with Widescreen displays
Shipping (Package) Weight	1.7 lb [0.8 kg]

Certifications, Reports and Compatibility

