

2 Port DVI Dual Monitor KVM Switch with PS/2
StarTech ID: SV221DVIDD



This compact 2-port dual monitor KVM switch (DVI+DVI) offers the ultimate in convenience and cost-savings.

The dual DVI KVM switch lets you instantly switch back and forth between PCs at the touch of a button, while maintaining professional-quality video on both monitors (high digital resolution of up to 1280 x 1024, analog resolutions up to 1920 x 1440).

An ideal solution for graphic designers, CAD/CAM designers or any project requiring dual view KVM control, the switch features a compact design, with cable entry positioned at the rear of the switch, saving valuable desk space and eliminating clutter.

A suitable multi-computer control solution for any workspace, the dual DVI KVM switch features a durable metal casing and is backed by our 2-year warranty and free lifetime technical support.

Applications and Solutions

- Designed for Dual DVI monitor enabled PCs
- Ideal for environments using desktops, workstations and servers with Flat Panel LCD monitors

Features

- DVI-I interface technology supports both digital and analog video signal transmission
- Switches instantly between two PCs
- Rear connections provide a neat and secure environment
- Supports PS/2 keyboards and mouse including M/S IntelliMouse, Explorer and Logitech NetMouse
- Keyboard and mouse are hot pluggable, eliminating the need to reboot your systems
- Operating system independent
- Front panel LED's indicate which computer is active
- Supports high digital resolution of up to 1280 x 1024 and analog resolution of up to 1920 x 1440
- Draws power from your computer's PS/2 port, does not require a power adapter
- HDCP Compliant

Technical Specifications

- Warranty: 2 Years
- Product Depth: 3.39 in [86 mm]
- Product Height: 2.44 in [62 mm]
- LED Indicators: 1 - Port Status (Numerical display)
- Maximum Number of Computers: 2
- Maximum Digital Resolutions: 1280x1024
- Maximum Analog Resolutions: 1920x1440 (not intended for use with Widescreen displays)
- Maximum Number of Users: 1
- Operating Temperature: 0°C to 40°C (32°F to 104°F)
- Output Current: 500mA
- Power Consumption: 0.5
- Carton Quantity: 10
- Shipping (Package) Weight: 1.92 lb [0.87 kg]
- Product Weight: 18.36 oz [520 g]
- Product Width: 5.51 in [140 mm]

