

2 Port DVI Dual Monitor KVM Switch with PS/2

StarTech ID: SV221DVIDD



This compact 2-port dual monitor KVM switch (DVI+DVI) offers the ultimate in convenience and cost-savings.

The dual DVI KVM switch lets you instantly switch back and forth between PCs at the touch of a button, while maintaining professional-quality video on both monitors (high digital resolution of up to 1280 x 1024, analog resolutions up to 1920 x 1440).

An ideal solution for graphic designers, CAD/CAM designers or any project requiring dual view KVM control, the switch features a compact design, with cable entry positioned at the rear of the switch, saving valuable desk space and eliminating clutter.

A suitable multi-computer control solution for any workspace, the dual DVI KVM switch features a durable metal casing and is backed by our 2-year warranty and free lifetime technical support.

Applications

- Designed for Dual DVI monitor enabled PCs
- Ideal for environments using desktops, workstations and servers with Flat Panel LCD monitors

Features

- DVI-I interface technology supports both digital and analog video signal transmission
- Switches instantly between two PCs
- Rear connections provide a neat and secure environment
- Supports PS/2 keyboards and mouse including M/S IntelliMouse, Explorer and Logitech NetMouse
- Keyboard and mouse are hot pluggable, eliminating the need to reboot your systems
- Operating system independent
- Front panel LED's indicate which computer is active
- Supports high digital resolution of up to 1280 x 1024 and analog resolution of up to 1920 x 1440
- Draws power from your computer's PS/2 port, does not require a power adapter
- HDCP Compliant

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	DVI
Multi-Monitor	Yes
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No
Console Interface(s)	2 - DVH (29 pin) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	4 - DVH (29 pin) Female
Host Connectors	4 - PS/2 (6 pin; Mini-DIN) Female
DVI Support	Yes
IP Control	No
Maximum Analog Resolutions	1920x1440 (not intended for use with Widescreen displays)
Maximum Digital Resolutions	1280x1024
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
Color	Black
Enclosure Type	Steel
Product Width	5.5 in [140 mm]
Product Height	2.4 in [62 mm]
Product Depth	3.4 in [86 mm]
Product Weight	18.4 oz [520 g]
LED Indicators	1 - Port Status (Numerical display)
Power Adapter Included	Optional
Output Voltage	9 DC
Output Current	0.5A
Power Consumption	0.5W
Operating Temperature	05/8/2012eg;C to 405/8/2012eg;C (325/8/2012eg;F to 1045/8/2012eg;F)
Shipping (Package) Weight	1.9 lb [0.9 kg]
Included in Package	1 - 2 Port KVM Switch
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

