

2 Port Micro PS/2 VGA Cable KVM Switch

StarTech ID: SV221MICRO



This 2-port Micro KVM switch lets you take command of two PS/2-controlled computers from a single console, without sacrificing any desk space.

A space-saving and cost-effective computer management solution, the compact Micro KVM switch can be hung or tied up out of the way to free up work space, and features ultra-thin cables built on to the switch, leaving zero footprint once installed.

The Micro KVM switch draws power from connected computers and doesn't require an external power source - eliminating the need to position the switch near an available power outlet and saving the space required for a power cable.

Don't let the size fool you! This high quality Micro KVM switch delivers robust display capability with support for resolutions up to 2048x1536 (@60Hz) and supports hot plug-and-play installation for easy deployment.

Designed to ensure a seamlessly dependable operating experience, the 2-port Micro KVM switch is backed by StarTech.com's 3-year warranty and free lifetime technical support.

Applications and Solutions

- Allows control of 2 computers from 1 user console
- Perfect for integrating two different enterprise computer systems

Features

- Automatically switch between 2 computer using the hot key commands
- Dependable 3-year Warranty
- Designed to integrate into your existing IT infrastructure and requires no software to be installed
- Plug n Play support allows users to change computers without any interruptions
- Supports MS Intellimouse (Pro Version), Explorer and Optical Mouse
- Ultra compact design and thin coaxial cables increases the availability and manageability of the server or workstation environment by using only one keyboard, monitor and a mouse

Technical Specifications

- Warranty: 3 Year warranty
- Connector Types: 2 - 6 DIN Female
- Connector Types: 4 - 6 DIN Male
- Connector Types: 1 - High Density DB15 Female
- Connector Types: 2 - High Density DB15 Male
- Enclosure Type: Plastic
- Product Height: 1.09 in [27.6 mm]
- Audio Support: No
- Cascadable: No
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: PS/2
- KVM IP Control: No
- Number of KVM Ports: 2
- Rack-Mountable: No
- KVM TFT: None
- Product Length: 2.98 in [75.6 mm]
- Maximum Number of Users: 1
- Carton Quantity: 10
- Shipping (Package) Weight: 1.04 lb [0.47 kg]
- Product Weight: 13.41 oz [380 g]
- Product Width: 0.46 in [1.18 cm]
- Compatibility: Compatible with all operating systems

- Enclosure: Plastic
- Keyboard: 6 Pin Mini DIN Female
- LED Indicators: 2 Indicators (CPU A & CPU B)
- Monitor: High Density DB15
- Mouse: 6 Pin Mini DIN Female
- Resolution: 2048x1536
- User Control Ports: 2
- General Specifications: 6 ft. cables attached

