

2 Port Micro PS/2 VGA Cable KVM Switch

StarTech ID: SV221MICRO



This 2-port Micro KVM switch lets you take command of two PS/2-controlled computers from a single console, without sacrificing any desk space.

A space-saving and cost-effective computer management solution, the compact Micro KVM switch can be hung or tied up out of the way to free up work space, and features ultra-thin cables built on to the switch, leaving zero footprint once installed.

The Micro KVM switch draws power from connected computers and doesn't require an external power source - eliminating the need to position the switch near an available power outlet and saving the space required for a power cable.

Don't let the size fool you! This high quality Micro KVM switch delivers robust display capability with support for resolutions up to 2048x1536 (@60Hz) and supports hot plug-and-play installation for easy deployment.

Designed to ensure a seamlessly dependable operating experience, the 2-port Micro KVM switch is backed by StarTech.com's 3-year warranty and free lifetime technical support.

Applications

- Allows control of 2 computers from 1 user console
- Perfect for integrating two different enterprise computer systems

Features

- Automatically switch between 2 computer using the hot key commands
- Dependable 3-year Warranty
- Designed to integrate into your existing IT infrastructure and requires no software to be installed
- Plug n Play support allows users to change computers without any interruptions
- Supports MS Intellimouse (Pro Version), Explorer and Optical Mouse
- Ultra compact design and thin coaxial cables increases the availability and manageability of the server or workstation environment by using only one keyboard, monitor and a mouse

Technical Specifications

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	2 - VGA (15 pin; High Density D-Sub) Male
Host Connectors	4 - PS/2 (6 pin; Mini-DIN) Male
DVI Support	No
IP Control	No
Maximum Analog Resolutions	2048x1536
Maximum Number of Users	1
Enclosure Type	Plastic
Cable Length	6 ft [1.8 m]
Product Length	3 in [75.6 mm]
Product Width	0.5 in [11.8 mm]
Product Height	1.1 in [27.6 mm]
Product Weight	13.4 oz [380 g]
LED Indicators	2 - CPU A/B Selection indicators
Shipping (Package) Weight	1 lb [0.5 kg]
Included in Package	1 - 2 Port Micro KVM on Cable
Included in Package	1 - Hot Key Reference Strip
Included in Package	1 - Instructional Manual

Certifications, Reports and Compatibility

