

2 Port Professional PS/2 KVM Switch

StarTech ID: SV231



This 2 Port PS/2 KVM Switch is a reliable computer management tool that allows you to control multiple computers from one source, minimizing downtime by making connected computers and input devices available as soon as they are attached.

This sturdy PS/2 KVM Switch features an all-metal, 1U chassis that adds to the unit's reliability and dependability.

The PS/2 KVM switch is designed to work with Dell, Compaq, IBM and HP servers, all PC notebook computers, and Compaq Alpha systems, and supports resolutions of up to 1920x1440 - ensuring a smooth and broadly compatible operating experience.

Applications

- Manufacturing line computer control
- PC test/burn-in computer control
- Dual system control for a single workstation

Features

- A dependable 3-year warranty provides peace of mind.
- Hot-pluggable to allow computers to be added or removed without worrying about having to reboot the other connected systems.
- Designed for guaranteed compatibility with Dell, Compaq, IBM and HP servers and systems.
- Compatible with all notebook computers.
- Compatible with Compaq Alpha systems.
- "Keep-alive" feature draws power from PC keyboard ports if power is lost. Switch will continue to operate during a power outage retaining complete control of all connected systems.
- Rugged, all-metal 1U chassis for use in harsh environments and space-saving cabinets.
- Fast switch-buttons for each port provide quick access to any connected system.
- High 1920x1440 resolution capability supports the most demanding applications.
- Uses standard off-the-shelf cables or StarTech.com tangle-free KVM cables to connect PCs to the switch
- All cables connect to the back of the switch reducing space requirements
- Completely operating system independent. No software or drivers required.

Technical Specifications

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	No
Daisy-Chain	Yes
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	2 - VGA (15 pin; High Density D-Sub) Male
Host Connectors	4 - PS/2 (6 pin; Mini-DIN) Female
DVI Support	No
IP Control	No
Maximum Analog Resolutions	1920 x 1440
Maximum Number of Users	1
Maximum Cascaded Computers	4
Enclosure Type	Steel
Product Length	2.8 in [70 mm]
Product Width	4.9 in [124 mm]
Product Height	1.6 in [40 mm]
Product Weight	14.8 oz [420 g]
Operating Temperature	05/10/2012eg;C to 405/10/2012eg;C (325/10/2012eg;F to 1045/10/2012eg;F)
Storage Temperature	-105/10/2012eg;C to 605/10/2012eg;C (145/10/2012eg;F to 1405/10/2012eg;F)
Humidity	0~80% RH
Shipping (Package) Weight	1.3 lb [0.6 kg]
Included in Package	1 - 2 Port StarView 2 KVM Switch
Included in Package	2 - PS/2 Mouse Connectors
Included in Package	4 - Rubber feet
Included in Package	1 - Hot-key Quick Reference
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

