

2 Port Dual DVI USB KVM Switch with Audio

StarTech ID: SV231DVIDDU



This 2 Port Dual DVI USB KVM Switch allows two PCs, each with dual DVI displays, to share two monitors, one microphone (and set of speakers), one keyboard and one mouse as well as two other USB peripherals.

An ideal solution for graphic designers, CAD/CAM designers or educational and financial institutions, the Dual DVI USB KVM Switch allows you to instantly switch back and forth between PCs at the touch of a button while maintaining professional level video quality on both DVI monitors, in turn saving money by eliminating redundant peripheral purchases.

Applications

- Control up to two computers with one keyboard, Mouse with dual display
- Can be used with computers that have a Dual Head DVI video card
- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications
- Integrated USB 2.0 hub and Mic/Audio switching allows the user to have full multimedia control of two computers and share USB peripherals

Features

- User-configurable simultaneous/independent switching of audio and USB hub ports or PC ports
- HDCP compliant
- USB style keyboard and mouse control, plus two other USB peripherals
- Direct channel selection and operation using front-panel push button and keyboard hotkeys
- Status LED display for easy port status monitoring
- Solid metal casing for the maximum durability
- Supports VESA DDC2B emulation and TMDS signal pass-through

Technical Specifications

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Multi-Monitor	Yes
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - DVH (29 pin) Female
Console Interface(s)	4 - USB A (4 pin) Female
Host Connectors	2 - USB B (4 pin) Female
Host Connectors	4 - 3.5 mm Mini-Jack (3 Position) Female
Host Connectors	4 - DVH (29 pin) Female
DVI Support	Yes
IP Control	No
Maximum Analog Resolutions	2048 x 1536 (analog) / 1920 x 1200 (digital)
Maximum Number of Users	1
Color	Black
Enclosure Type	Steel
Product Length	6.4 in [163 mm]
Product Width	3.9 in [100 mm]
Product Height	2.6 in [66 mm]
Product Weight	25.8 oz [730 g]
Power Adapter Included	Yes
Output Voltage	9 DC
Output Current	1.7A
Center Tip Polarity	Positive
Shipping (Package) Weight	2.9 lb [1.3 kg]
Included in Package	1 - 2 port Dual DVI KVM Switch
Included in Package	1 - Power Adapter
Included in Package	1 - Software CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

