

2 Port Professional USB KVM Switch Kit with Cables

StarTech ID: SV231USB



This 2 Port USB KVM Switch Kit offers simple control of two Mac or PC computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The switch includes two USB KVM cables, to providing a complete out-of-the-box KVM solution while saving you time and money.

The USB KVM switch features an integrated 3 port USB hub, allowing you to share connected USB peripherals between the two controlled PC/Mac computers as though the devices were connected directly to the computers.

Ensuring convenient placement and installation, the KVM switch features a compact form factor design and offers rear-port connection to master and slave computers, allowing you to make the necessary device connections without disrupting your workspace.

A cross-platform solution, the KVM switch supports high resolution applications at up to 1920x1400 display resolutions, and provides a smooth operating experience when controlling Mac/PC combined work environments.

Applications and Solutions

- Dual system control for a single workstation
- Manufacturing line computer control

- PC test/burn-in computer control

Features

- 2 computers can share 3 different USB peripherals.
- Control 2 PCs, G3/G4 Macs or iMacs from one USB keyboard/mouse/monitor.
- Front panel push buttons for easy computer selection.
- No drivers required for keyboard and mouse operation.
- Selectable auto scan time interval.
- Supports keyboard and mouse plug and play.
- Supports the latest DDC2B VGA monitors.
- USB self-power operation.

Technical Specifications

- Warranty: 3 Year warranty
- Color: Black
- Connector Types: 3 - USB A Female
- Connector Types: 2 - USB B Female
- Connector Types: 1 - High Density DB15 Female
- Connector Types: 2 - High Density DB15 Male
- Enclosure Type: Steel
- Product Height: 1.57 in [40 mm]
- Audio Support: No
- Cascadable: No
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: USB
- KVM IP Control: No
- Number of KVM Ports: 2
- Rack-Mountable: No
- KVM TFT: None
- Product Length: 4.88 in [124 mm]
- Maximum Number of Computers: 2
- Maximum Analog Resolutions: 1920 x 1440
- Maximum Number of Users: 1

- Power Adapter Included: Yes
- Power Adapter - Amperage: 2A
- Power Adapter - DC Voltage: 5V
- Center Tip Polarity: Positive
- Carton Quantity: 6
- U Height: 1
- Shipping (Package) Weight: 2.96 lb [1.34 kg]
- Product Weight: 14.83 oz [420 g]
- Product Width: 2.76 in [70 mm]
- Hot Plug Capability: Yes
- Auto Scan Intervals: 3, 8, 15 and 30 seconds
- Cable Length (Max): VGA-100ft (30m) USB-15ft (5m)
- Cables Included: 2 x 6ft USB KVM cables
- MTBF: 111,383 Hours

