

2 Port Professional USB KVM Switch Kit with Cables

StarTech ID: SV231USB



The SV231SUB 2 Port Professional USB KVM Switch Kit with Cables offers simple control of two Mac or PC computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The 2 Port KVM switch includes 2 USB KVM cables, providing a complete out-of-the-box KVM solution saving you time and money. An integrated 3 port USB hub allows you to share connected USB peripherals between connected computers as though they were connected directly. A compact form factor design and rear-port connections to master and slave computers minimizes disruption to your workspace.

A cross-platform solution, this OS independent KVM switch supports high resolution applications up to 1920x1440, and provides a smooth operating experience when controlling mixed (Windows/Mac/Linux) environments.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Applications

- Dual system control for a single workstations increasing user productivity in the office
- Provide centralized control for multiple high-res Digital Signage server control
- Great for manufacturing line computer control, simplifying access to multiple systems
- Perfect for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice

Features

- Control 2 computers from one USB keyboard/mouse/monitor
- Share 3 different USB peripherals using the integrated hub
- High 1920x1440 resolution capability
- Front panel push buttons for easy computer selection
- OS independent - No software or drivers required
- Supports keyboard and mouse plug and play
- Selectable auto scan time interval
- Supports DDC2B VGA monitors
- USB self-power operation

Technical Specifications

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
U Height	1U
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	3 - USB A (4 pin) Female
Host Connectors	2 - USB B (4 pin) Female
Host Connectors	2 - VGA (15 pin; High Density D-Sub) Male
DVI Support	No
IP Control	No
Maximum Cable Length	15 ft [4.6 m]
Maximum Analog Resolutions	1920 x 1440
Auto Scan	3, 8, 15 & 30 seconds
Maximum Number of Users	1
MTBF	111,383 Hours
Color	Black
Enclosure Type	Steel
Product Length	4.9 in [124 mm]
Product Width	2.8 in [70 mm]
Product Height	1.6 in [40 mm]
Product Weight	14.8 oz [420 g]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	0.4A
Output Voltage	5 DC

Output Current 2A

Center Tip Polarity Positive

Plug Type N

Note This KVM supports the use of VGA cables up to 100ft in length - active extension required for USB to achieve that distance

Shipping (Package) Weight 3 lb [1.3 kg]

Included in Package 1 - 2 Port USB KVM Switch

Included in Package 2 - 2 IN 1 USB/VGA Cables

Included in Package 1 - Power Adapter

Included in Package 1 - Manual

Certifications, Reports and Compatibility

