

2 Port Steel USB KVM Switch with Audio and USB 2.0 Hub

StarTech ID: SV231USBA



The SV231USBA 2-port USB KVM switch offers native USB control of 2 computers using a single keyboard, mouse and VGA monitor peripheral set.

A versatile addition to any operating environment, this versatile USB KVM switch is suitable for graphics-intensive applications, with support for display resolutions of up to 2048x1536 pixels.

A complete multimedia switching solution, the KVM Switch also supports audio switching between connected computers and allows you to "lock on" to the desired audio from one computer, even if you're controlling a different computer.

Saving both install space and expense, the 2-port USB KVM switch features an integrated USB 2.0 hub that enables you to share high speed USB devices between computers, as if the peripheral devices were connected directly to the controlled (slave) computers - a cost-effective solution that eliminates the cost of duplicate peripheral purchases, with no compromise on functionality.

Designed to provide a dependable computer control solution, the USB KVM switch is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Please Note: If you are using 2-in-1 KVM cables with this switch, the (GC15HSM) [Slimline VGA Gender Changer](#) is required.

Applications

- Controlling two computers using a single keyboard, mouse and monitor
- Integrated USB 2.0 hub allows you to share USB peripherals between computers

Features

- Designed for high-resolution applications: up to 2048 x 1536 pixels supported
- Hotkey switching for ease-of-use
- Metal chassis for long-term durability
- Integrated USB 2.0 hub allows you to share high-speed USB devices between computers
- Audio can be locked to a particular port when switching between computers

Technical Specifications

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	2 - USB B (4 pin) Female
Host Connectors	2 - VGA (15 pin; High Density D-Sub) Female
Host Connectors	4 - 3.5 mm Mini-Jack (3 Position) Female
Other Interface(s)	2 - USB A (4 pin) Female
DVI Support	No
IP Control	No
Maximum Analog Resolutions	2048 x 1536
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
Color	Black
Enclosure Type	Steel
Product Length	6.5 in [165 mm]
Product Width	3.9 in [100 mm]
Product Height	1.8 in [45 mm]
Product Weight	35.3 oz [1000 g]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Output Voltage	9 DC
Output Current	1A
Center Tip Polarity	Positive
Plug Type	M
Shipping (Package) Weight	3 lb [1.4 kg]

Included in Package	1 - 2 Port KVM Switch
Included in Package	1 - Power Adapter
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

