

## 2 Port USB KVM Switch with Ethernet Switch and Audio & USB Hub

StarTech ID: SV231USBAN



This 2 Port USB KVM Switch is a multi-function switch that integrates a USB 2.0 hub, Ethernet Switch, and audio switching capability into a unique USB KVM multimedia switching solution.

For simple integration into multimedia applications, the switch supports high resolution VGA video interfaces and allows you to toggle between audio sources. The KVM switch also provides a built-in 3 port 10/100 Mbps Ethernet Switch that allows you to easily network and share Internet connectivity among connected computers while reducing the number of outlets and cables needed in the area - helping to preserve valuable work space.

Plus, the KVM switch also features a built-in USB 2.0 Hub that allows peripheral sharing for printers, scanners, portable hard drives, etc., with support for hi-speed USB 2.0 data transfer rates of up to 480 Mbps.

This USB KVM Switch is cased in a sturdy metal chassis, and offers a compact form factor that helps preserve valuable desk space.

For a downloadable benefits sheet [click here](#)

### Applications and Solutions

- Ideal for financial/banking industries, graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are needed
- Great for imaging machines where network connections are limited

## Features

- 2-year Warranty
- Multi-function USB KVM switch integrates a USB 2.0 hub, Ethernet switch, and audio
- Controls two computers with a single VGA monitor, USB keyboard and mouse
- Built-in USB 2.0 Hub allows peripheral sharing for printers, scanners, portable hard drives, etc., with data transfer rates of up to 480 Mbps
  - Built-in 3 port 10/100 Mbps Ethernet Switch allows you to easily network and share Internet with your computers
  - Hot pluggable - add or remove computers without powering down the switch
  - Supports Windows 98/SE/ME/2000/XP/Vista, Linux, MacOS, etc.
  - Bi-directional switching and flexible interoperability; switch permits independent PC, independent peripheral, and independent audio function, regardless of KVM switch focus

## Technical Specifications

- Warranty: 2 Years
- Product Depth: 3.18 in [80.7 mm]
- Product Height: 1.99 in [5.05 cm]
- Humidity: 0 ~ 80% RH
- Cable Length: Two 6ft (1.8m) KVM Cables
- LED Indicators: Orange - PC Activity and Select indicator
- LED Indicators: Green - Indicates a USB connection to USB HUB
- LED Indicators: Green - Ethernet Link and Activity
- Maximum Analog Resolutions: 2048 x 1536
- Operating Temperature: 0 ~ 50°C
- Output Current: 2400mA
- Carton Quantity: 5
- Storage Temperature: -20 ~ 60°C
- Shipping (Package) Weight: 3.71 lb [1.68 kg]
- Product Weight: 2.03 lb [0.92 kg]
- Product Width: 10.63 in [27 cm]

