

4 Port Black PS/2 KVM Switch Kit with Cables

StarTech ID: SV411K



The SV411K 4 Port Black PS/2 KVM Switch Kit with cables lets you control four computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch supports video resolutions of up to 2048 x 1536 and includes 3-in-1 (PS/2 and Video) cables to provide a complete, out-of-the-box KVM solution.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Control 4 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Ideal for call centers, help desks, education environments, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Multiple system control for single user workstations, increasing user productivity in the office

Features

- Unique 3-in-1 cables included prevent keyboard and mouse connectors from becoming loose
- Supports PS/2 keyboard and mouse emulation for error-free PC boot
- All cables are connected to the rear for a more secure and neat connection
- Keyboard and mouse allow for hot plugging without having to turn either the KVM or the PC off
- Supports M/S IntelliMouse(Pro), Explorer, Optical mice
- Auto Scan Interval: 3, 8, 15, 30 seconds

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	4
PC Interface	PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	4 - VGA (15 pin; High Density D-Sub) Female
DVI Support	No
IP Control	No
Maximum Cable Length	2 x 4ft(1.2m) and 2 x 6ft(1.8m) included
Maximum Analog Resolutions	1920 x 1440
Maximum Number of Users	1
Color	Black
Enclosure Type	Plastic
Product Length	7.3 in [185 mm]
Product Width	3.4 in [86 mm]
Product Height	0.9 in [22 mm]
Power Adapter Included	Self Powered
Shipping (Package) Weight	3.1 lb [1.4 kg]
Included in Package	1 - 4 Port Compact KVM switch
Included in Package	4 - KVM Cables
Included in Package	1 - Set of rubber feet
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

