

4 Port Tower Style PS/2 KVM Switch Kit with Cables

StarTech ID: SV411KT



This 4-port tower style KVM Switch Kit lets you control multiple PS/2 computers from a single console (keyboard, mouse, monitor), saving equipment costs while providing a convenient operating platform.

A perfect console-sharing solution for SOHO, help desks and call centers, the KVM switch supports display resolutions of up to 1920x1440 as well as plug-and-play connectivity, which eliminates the hassle of having to power down computers to be connected to the switch. To ensure error-free bootups, the KVM switch supports PS/2 keyboard and mouse emulation.

The KVM switch offers both keyboard hotkey and front panel push-button control, and features a compact and lightweight mini-tower design with rear panel cable connections, saving valuable workspace.

Providing an out-of-the-box KVM solution, the tower style switch includes four 3-in-1 tangle-free cables and is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Applications

- Lets you instantly control four PS/2 computers from a single keyboard, mouse and monitor
- Compatible with desktops, workstations, servers, and laptops
- Useful for call centers, help desks, education environments, home gamers and PC enthusiasts

Features

- Unique 3-in-1 cables prevent keyboard and mouse connectors from becoming loose
- Lightweight, compact mini tower
- Rear cable connections keep your desktop neat and tangle free
- Supports PS/2 keyboard and mouse emulation for error-free PC bootup
- Hot pluggable keyboard and mouse ports allow easy connections without having to reboot your systems
- Compatible with all operating systems
- Supports high VGA resolution of up to 1920x1440
- Power-free operation, draws power from attached computers and requires no external power adapters
- Port selection using push button or keyboard commands
- Supports Logitech Mouseman, and MS Intellimouse (Ver 2.0 and earlier).
- Supports PS/2 keyboard and mouse emulation for error-free PC bootup
- Draws power from computer, requiring no external power adapter

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	4
PC Interface	PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
Industry Standards	DDC2B
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	4 - VGA (15 pin; High Density D-Sub) Female
DVI Support	No
IP Control	No
Maximum Analog Resolutions	1920x1440
Auto Scan	3, 8, 15 & 30 seconds
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
OS Compatibility	OS Independent
Color	Black
Enclosure Type	Plastic
Product Length	3.9 in [100 mm]
Product Width	2 in [50 mm]
Product Height	5 in [126 mm]
Product Depth	3.9 in [100 mm]
Product Weight	7.2 oz [204 g]
LED Indicators	4 - Port Status
Shipping (Package) Weight	2.7 lb [1.2 kg]
Included in Package	1 - 4 Port KVM
Included in Package	4 - 6ft(1.83m) KVM Cables
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

