

4 Port VGA Dual Monitor KVM Switch with PS/2

StarTech ID: SV421DD



This compact 4-port dual monitor KVM switch (VGA+VGA) offers the ultimate in convenience and cost-savings.

The dual VGA KVM switch lets you instantly switch back and forth between PCs at the touch of a button, while maintaining professional-quality video (up to 1920x1440) on both monitors.

An ideal solution for graphic designers, CAD/CAM designers or any project requiring dual monitor KVM control, the switch features a compact design, with cable entry positioned at the rear of the switch, saving valuable desk space and eliminating clutter.

A suitable multi-computer control solution for any workspace, the dual view KVM switch features a durable metal casing and is backed by our 2-year warranty and free lifetime technical support.

Applications and Solutions

- Control up to 4 computers with 1 keyboard, Mouse and 2 monitors
- Used in computers with Dual-VGA Cards
- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications

Features

- Offers direct channel selection using front panel push button and keyboard hotkeys
- Supports a high VGA resolution of up to 1920 x 1440 pixels
- All cables are connected to the rear for a more secure and neat connection
- Supports hot-plugging of PS/2 keyboards and mice including M/S IntelliMouse, Explorer, Optical mice and Logitech

Netmouse

- Operating system independent, compatible with all operating systems
- Buzzer sound for port switching confirmation
- Front panel LED's indicate which computer is active
- Power-free operation draws power from attached computers and requires no power adapters
- Numerical LED indicator for easy port status monitoring

Technical Specifications

- Warranty: 2 Years
- Product Depth: 3.94 in [100 mm]
- Product Height: 2.62 in [66.5 mm]
- Maximum Number of Computers: 4
- Maximum Analog Resolutions: 1920x1440
- Maximum Number of Users: 1
- Operating Temperature: 0°C to 40°C (32°F to 104°F)
- Carton Quantity: 10
- Storage Temperature: -20°C to 60°C (-4°F to 140°F)
- U Height: 1.5
- Shipping (Package) Weight: 2.94 lb [1.33 kg]
- Product Weight: 35.3 oz [1000 g]
- Product Width: 7.87 in [200 mm]

