

## 4 Port VGA Dual Monitor KVM Switch with PS/2

StarTech ID: SV421DD



This compact 4-port dual monitor KVM switch (VGA+VGA) offers the ultimate in convenience and cost-savings.

The dual VGA KVM switch lets you instantly switch back and forth between PCs at the touch of a button, while maintaining professional-quality video (up to 1920x1440) on both monitors.

An ideal solution for graphic designers, CAD/CAM designers or any project requiring dual monitor KVM control, the switch features a compact design, with cable entry positioned at the rear of the switch, saving valuable desk space and eliminating clutter.

A suitable multi-computer control solution for any workspace, the dual view KVM switch features a durable metal casing and is backed by our 2-year warranty and free lifetime technical support.

### Applications

- Control up to 4 computers with 1 keyboard, Mouse and 2 monitors
- Used in computers with Dual-VGA Cards
- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications

## Features

- Offers direct channel selection using front panel push button and keyboard hotkeys
- Supports a high VGA resolution of up to 1920 x 1440 pixels
- All cables are connected to the rear for a more secure and neat connection
- Supports hot-plugging of PS/2 keyboards and mice including M/S IntelliMouse, Explorer, Optical mice and Logitech Netmouse
- Operating system independent, compatible with all operating systems
- Buzzer sound for port switching confirmation
- Front panel LED's indicate which computer is active
- Power-free operation draws power from attached computers and requires no power adapters
- Numerical LED indicator for easy port status monitoring

## Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	4
PC Interface	PS/2
PC Video Type	VGA
Multi-Monitor	Yes
Rack-Mountable	No
Cables Included	No
U Height	1.5U
Daisy-Chain	No
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Console Interface(s)	2 - VGA (15 pin; High Density D-Sub) Female
Host Connectors	8 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	8 - VGA (15 pin; High Density D-Sub) Female
DVI Support	No
IP Control	No
Maximum Analog Resolutions	1920x1440
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
Color	Black
Enclosure Type	Steel
Product Width	7.9 in [200 mm]
Product Height	2.6 in [66.5 mm]
Product Depth	3.9 in [100 mm]
Product Weight	35.3 oz [1000 g]
Operating Temperature	05/11/2012eg;C to 405/11/2012eg;C (325/11/2012eg;F to 1045/11/2012eg;F)
Storage Temperature	-205/11/2012eg;C to 605/11/2012eg;C (-45/11/2012eg;F to 1405/11/2012eg;F)
Shipping (Package) Weight	2.9 lb [1.3 kg]
Included in Package	1 - 4 Port KVM Switch
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

