

## 4 Port StarView DVI KVM Switch

StarTech ID: SV421DVI



Experience crystal-clear digital images on all your PCs without the cost of multiple flat-panel monitors. Our StarView DVI KVM switch lets you share one flat panel monitor, PS/2 keyboard, and PS/2 mouse between four computers, so you'll be able to sit back and enjoy razor-sharp digital images while effortlessly flipping between your PCs. Designed specifically for DVI flat panel displays, this KVM switch preserves the integrity of your digital images, making sure distortion and signal loss is kept to a minimum.

Like all our StarView KVM switches, the SV421DVI offers convenient features like hot-key commands and auto-scanning. And since desk space is usually at a premium, we've designed the SV421DVI to have all its cable connections in the rear to keep things neat.

### Applications

- Enables users to control 4 computers from 1 Keyboard, Mouse and Flat Panel LCD monitor
- Ideal for environments using desktops, workstations and servers with Flat Panel LCD monitor
- Switches instantly between two PCs

## Features

- DVI-I interface technology supports both digital and analog video signal transmission
- All cables are connected to the rear for a more secure and neat connection
- Supports PS/2 keyboards and mouse including M/S IntelliMouse (Pro), Explorer and Optical mice
- Keyboard and mouse allow for hot plugging without having to turn either the KVM or the PC off
- Operating system independent, compatible with all operating systems
- Front panel LED's indicate which computer is active
- Supports high digital resolution of up to 1280x1024 and analog resolution of up to 1920x1440
- Power-free operation draws power from your computer's PS/2 port and requires no power adapters
- Buzzer sound for port switching confirmation
- HDCP Compliant

## Technical Specifications

Warranty 2 Years

Audio No

KVM Ports 4

PC Interface PS/2

Multi-Monitor No

Rack-Mountable No

U Height 1.5U

Daisy-Chain No

DVI Support Yes

IP Control No

Maximum Analog Resolutions 1920 x 1440

Maximum Digital Resolutions 1280 x 1024

Maximum Number of Users 1

### General Specifications

General Specifications 0<sup>0</sup>C ~ 40<sup>0</sup>C

General Specifications 2.2 Lbs (1 Kgs)

General Specifications DVI: 1 x DVH Dual Link (female)

General Specifications DVI: 4 x DVH Dual Link (female)

General Specifications FCC & CE

General Specifications Height: 1.75 Inches (45 mm)

General Specifications Keyboard: 1 x PS/2 6-pin Mini Din (female)

General Specifications Keyboard: 4 x PS/2 6-pin Mini Din (female)

General Specifications Length: 4.25 Inches (107 mm)

General Specifications Metal

General Specifications Mouse: 1 x PS/2 6-pin Mini Din (female)

General Specifications Mouse: 4 x PS/2 6-pin Mini Din (female)

General Specifications Port Status (Numerical display)

General Specifications PS/2 interface & 9V 500mA Adapter (optional)

General Specifications Push Button and Hot Keys

General Specifications Width: 8.75 Inches (223 mm)

Color Black

Enclosure Type Steel

Product Length 8.7 in [220 mm]

Product Width 3.9 in [100 mm]

Shipping (Package) Weight	2.5 lb [1.1 kg]
Connector Type(s)	10 - PS/2 (6 pin; Mini-DIN) Female
Connector Type(s)	5 - DVH (29 pin) Female

**Certifications, Reports and Compatibility**

