

## 4 Port DVI Dual Monitor KVM Switch with PS/2

StarTech ID: SV421DVIDD



This compact 4-port dual monitor KVM switch (DVI+DVI) offers the ultimate in convenience and cost-savings.

The dual DVI KVM switch lets you instantly switch back and forth between PCs at the touch of a button, while maintaining professional-quality video on both monitors (high digital resolution of up to 1280 x 1024, analog resolutions up to 1920 x 1440).

An ideal solution for graphic designers, CAD/CAM designers or any project requiring dual view KVM control, the switch features a compact design, with cable entry positioned at the rear of the switch, saving valuable desk space and eliminating clutter.

A suitable multi-computer control solution for any workspace, the dual DVI KVM switch features a durable metal casing and is backed by our 2-year warranty and free lifetime technical support.

### Applications and Solutions

- Designed for Dual DVI monitor enabled PCs
- Ideal for environments using desktops, workstations and servers with Flat Panel LCD monitors

## **Features**

- DVI-I interface technology supports both digital and analog video signal transmission
- Switches instantly between two PCs
- Rear connections provide a neat and secure environment
- Supports PS/2 keyboards and mouse including M/S IntelliMouse, Explorer and Logitech NetMouse
- Keyboard and mouse are hot pluggable, eliminating the need to reboot your systems
- Operating system independent
- Front panel LED's indicate which computer is active
- Supports high digital resolution of up to 1280 x 1024 and analog resolution of up to 1920 x 1440
- Draws power from your computer's PS/2 port, does not require a power adapter
- HDCP Compliant

## Technical Specifications

- Warranty: 2 Years
- Product Height: 2.68 in [6.8 cm]
- Product Length: 8.74 in [22.2 cm]
- Maximum Number of Computers: 4
- Maximum Digital Resolutions: 1280 x 1024
- Maximum Analog Resolutions: 1920 x 1440
- Maximum Analog Resolutions: This product is not intended for use with Widescreen displays.
- Maximum Number of Users: 1
- Power Consumption: 0.5
- Carton Quantity: 5
- U Height: 1.5
- Shipping (Package) Weight: 3.05 lb [1.38 kg]
- Product Width: 4.13 in [10.5 cm]
- PC Connectors: Keyboard: 4 x PS/2 6-pin Mini Din (female)
  - Mouse: 4 x PS/2 6-pin Mini Din (female)
  - DVI: 8 x DVI-I Dual Link (female)
- Console Connector: : Keyboard: 1 x PS/2 6-pin Mini Din (female)
  - Mouse: 1 x PS/2 6-pin Mini Din (female)
  - DVI: 2 x DVI-I Dual Link (female)
- Port Selection: Push Button and Hot Keys
- Power: PS/2 interface & 9V 500mA Adapter (optional)
- Operating temperature: 00C ~ 400C
- LED Indicator: Port Status (Numerical display)
- Dimensions: Length: 8.6 Inches (220 mm)
  - Width: 3.9 Inches (100 mm)
  - Height: 2.6 Inches (66.5 mm)
- Weight: 2.2 Lbs (1.0 Kgs)
- Enclosure: Metal
- Safety Standards: FCC & CE

