

4 Port DVI Dual Monitor KVM Switch with PS/2

StarTech ID: SV421DVIDD



This compact 4-port dual monitor KVM switch (DVI+DVI) offers the ultimate in convenience and cost-savings.

The dual DVI KVM switch lets you instantly switch back and forth between PCs at the touch of a button, while maintaining professional-quality video on both monitors (high digital resolution of up to 1280 x 1024, analog resolutions up to 1920 x 1440).

An ideal solution for graphic designers, CAD/CAM designers or any project requiring dual view KVM control, the switch features a compact design, with cable entry positioned at the rear of the switch, saving valuable desk space and eliminating clutter.

A suitable multi-computer control solution for any workspace, the dual DVI KVM switch features a durable metal casing and is backed by our 2-year warranty and free lifetime technical support.

Applications

- Designed for Dual DVI monitor enabled PCs
- Ideal for environments using desktops, workstations and servers with Flat Panel LCD monitors

Features

- DVI-I interface technology supports both digital and analog video signal transmission
- Switches instantly between two PCs
- Rear connections provide a neat and secure environment
- Supports PS/2 keyboards and mouse including M/S IntelliMouse, Explorer and Logitech NetMouse
- Keyboard and mouse are hot pluggable, eliminating the need to reboot your systems
- Operating system independent
- Front panel LED's indicate which computer is active
- Supports high digital resolution of up to 1280 x 1024 and analog resolution of up to 1920 x 1440
- Draws power from your computer's PS/2 port, does not require a power adapter
- HDCP Compliant

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	4
PC Interface	PS/2
PC Video Type	DVI
Multi-Monitor	Yes
Rack-Mountable	No
Cables Included	No
U Height	1.5U
Daisy-Chain	No
Console Interface(s)	2 - DVH (29 pin) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	8 - DVH (29 pin) Female
Host Connectors	8 - PS/2 (6 pin; Mini-DIN) Female
DVI Support	Yes
IP Control	No
Maximum Analog Resolutions	1920 x 1440
Maximum Digital Resolutions	1280 x 1024
Maximum Number of Users	1
General Specifications	: Keyboard: 1 x PS/2 6-pin Mini Din (female)
General Specifications	00C ~ 400C
General Specifications	2.2 Lbs (1.0 Kgs)
General Specifications	DVI: 2 x DVH Dual Link (female)
General Specifications	DVI: 8 x DVH Dual Link (female)
General Specifications	FCC & CE
General Specifications	Height: 2.6 Inches (66.5 mm)
General Specifications	Keyboard: 4 x PS/2 6-pin Mini Din (female)
General Specifications	Length: 8.6 Inches (220 mm)
General Specifications	Metal
General Specifications	Mouse: 1 x PS/2 6-pin Mini Din (female)
General Specifications	Mouse: 4 x PS/2 6-pin Mini Din (female)
General Specifications	Port Status (Numerical display)
General Specifications	PS/2 interface & 9V 500mA Adapter (optional)
General Specifications	Push Button and Hot Keys

General Specifications	Width: 3.9 Inches (100 mm)
Color	Black
Enclosure Type	Steel
Product Length	8.7 in [222 mm]
Product Width	4.1 in [105 mm]
Product Height	2.7 in [68 mm]
Power Consumption	0.5W
Note	This product is not intended for use with widescreen displays
Shipping (Package) Weight	3 lb [1.4 kg]

Certifications, Reports and Compatibility

