

## 4 Port High Resolution USB DVI Dual Link KVM Switch with Audio

StarTech ID: SV431DVIUAHR



This 4 Port Dual Link DVI USB KVM Switch provides simple, yet comprehensive control of up to four directly connected computers as well as audio switching capability and support for high resolution applications (supports 1080p, and up to 2560x1600 @ 60Hz, up to 3840 x 2400 at lower refresh rates, and Apple Cinema quality resolutions) - a superior switching solution that integrates perfectly into multimedia environments.

The DVI USB KVM Switch is compatible with all USB supported operating systems, and features a built-in USB 2.0 hub that allows you to share up to three high speed USB devices between computers.

### Applications and Solutions

- Designed for large and high resolution displays such as Multimedia Display, Apple Cinema Displays, Stock trading setups, and Medical Displays.
- Ideal for using desktops, workstations and servers with Ultra High resolution displays
- Sharing computers and USB devices in the home/SOHO/multimedia environment
- Switches instantly between PCs
- Switching USB peripherals between PC's

## Features

- All metal chassis for long-term durability
- Compatible with all USB supported Operating Systems
- Designed for high-resolution applications: 2560x1600 @ 60Hz: Higher resolutions (3840 x 2400) are supported at lower refresh rates.
- Front panel push button computer selection
- HDCP Compliant
- Integrated USB 2.0 hub allows you to share up to three high-speed USB devices between computers

## Technical Specifications

- Warranty: 3 Year warranty
- Color: Black
- Carton Quantity: 6
- Enclosure Type: Steel
- Audio Support: Yes
- DVI Support: Yes
- Supported Platforms: USB
- Rack-Mountable: Yes
- Maximum Analog Resolutions: 2560x1600 @ 60Hz
- Number of KVM Ports: 4
- Console Connectors: 1 x DVI female
  - 1 x USB 2.0 hub Type A
  - 1 x 3.5mm Microphone
  - 1 x 3.5mm Speaker
- Host Connectors : 4 x DVI female
  - 4 x USB Type B female
  - 4 x 3.5mm Microphone
  - 4 x 3.5mm Speaker
- Power Adapter Included: Yes
- Power Adapter - DC Voltage: 5
- Power Adapter - Amperage: 2.0
- Operating Temperature: 0 ~ 40
- Center Tip Polarity: Positive

- Product Height: 1.73 in [4.4 cm]
- Product Length: 8.66 in [22 cm]
- Product Width: 5.12 in [13 cm]
- Product Weight: 3.87 lb [1.75 kg]
- Shipping (Package) Weight: 2.74 lb [1.24 kg]
- **Note:** Resolutions exceeding 2560x1600 can be obtained by using a lower refresh rate. Example 3840x2400 @30Hz

