

## 4 Port Steel USB KVM Switch with Audio and USB 2.0 Hub

StarTech ID: SV431USBA



This 4-port USB KVM switch offers native USB control of 4 computers using a single keyboard, mouse and VGA monitor peripheral set.

A versatile addition to any operating environment, the USB KVM switch is suitable for graphics-intensive applications, with support for display resolutions of up to 2048x1536 pixels.

A complete multimedia switching solution, the USB KVM Switch also supports audio switching between connected computers and allows you to "lock on" to the desired audio from one computer even if you're controlling a different computer.

Saving both install space and expense, this USB 4-port KVM switch features an integrated USB 2.0 hub, which enables you to share high-speed USB devices between computers, as if the peripheral devices were connected directly to the controlled (slave) computers - a cost-effective solution that eliminates the cost of duplicate peripheral purchases, with no compromise on functionality.

Designed to provide a dependable computer control solution, the USB KVM switch is backed by StarTech.com's 2-year warranty and free lifetime technical support.

**Please Note:** If you are using 2-in-1 KVM cables with this switch, the (GC15HSM) [Slimline VGA Gender Changer](#) is required.

### Applications

- Controlling two computers using a single keyboard, mouse and monitor
- Integrated USB 2.0 hub allows you to share USB peripherals between computers

## Features

- Designed for high-resolution applications: up to 2048 x 1536 pixels supported
- Hotkey switching for ease-of-use
- Metal chassis for long-term durability
- Integrated USB 2.0 hub allows you to share high-speed USB devices between computers
- Audio or USB can be locked to a particular port when switching between computers

## Technical Specifications

|                            |   |
|----------------------------|---|
| Warranty                   | 2 Years                                     |
| Audio                      | Yes   |
| KVM Ports                  | 4   |
| PC Interface               | USB   |
| PC Video Type              | VGA   |
| Multi-Monitor              | No  |
| Rack-Mountable             | No  |
| Cables Included            | No  |
| Daisy-Chain                | No  |
| Console Interface(s)       | 1 - VGA (15 pin; High Density D-Sub) Female |
| Console Interface(s)       | 2 - 3.5 mm Mini-Jack (3 Position) Female    |
| Console Interface(s)       | 2 - USB A (4 pin) Female                    |
| Host Connectors            | 4 - USB B (4 pin) Female                    |
| Host Connectors            | 4 - VGA (15 pin; High Density D-Sub) Female |
| Host Connectors            | 8 - 3.5 mm Mini-Jack (3 Position) Female    |
| Other Interface(s)         | 2 - USB A (4 pin) Female                    |
| DVI Support                | No  |
| IP Control                 | No  |
| Maximum Analog Resolutions | 2048x1536                                   |
| Maximum Number of Users    | 1   |
| Port Selection Support     | Push Button and Hotkeys                     |
| Color                      | Black                                       |
| Enclosure Type             | Steel                                       |
| Product Width              | 10 in [255 mm]                              |
| Product Height             | 1.8 in [45 mm]                              |
| Product Depth              | 4.5 in [115 mm]                             |
| Product Weight             | 63.5 oz [1800 g]                            |
| Power Adapter Included     | Yes   |
| Shipping (Package) Weight  | 3.9 lb [1.8 kg]                             |
| Included in Package        | 1 - 4 Port KVM Switch                       |
| Included in Package        | 1 - Power Adapter                           |
| Included in Package        | 1 - User Manual                             |

Certifications, Reports and Compatibility

