

## USB PS2 KVM Console Extender Cat5 Extender - 500 ft

StarTech ID: SV565UTP



The SV565UTP USB PS2 KVM Console Extender Cat5 Extender (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away.

Use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

For added convenience, the Console/KVM extender supports both USB and PS/2 computer connections, and is compatible with any brand of KVM Switch.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Use one or more servers in a server room from a remote location
- Monitor computer-controlled equipment in a factory or warehouse

### Features

- Can be used with a single computer or connected to an existing KVM switch
- Supports auto-switching between host and remote users or dedicated control
- Both USB and PS/2-based computers are supported at the host and remote locations (PS/2 keyboard and mouse required for remote console)
- Easy installation using industry-standard UTP network cable
- Intuitive hotkey commands

## Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB and PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	1 - VGA (15 pin; High Density D-Sub) Female
Other Interface(s)	1 - RJ-45 Female
IP Control	No
Maximum Cable Length	500 ft. (150m)
Supported Resolutions	1280x1024 @ 300ft/ 100m 1024x768 @ maximum cable length
Color	Black
Product Length	3 in [7.5 cm]
Product Width	6.1 in [15.5 cm]
Product Height	0.8 in [2 cm]
Product Weight	10.6 oz [299 g]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	0.2A
Output Voltage	9 DC
Output Current	0.6A
Center Tip Polarity	Positive
Plug Type	M
Operating Temperature	05/8/2012eg;C to 405/8/2012eg;C (325/8/2012eg;F to 1045/8/2012eg;F)
Storage Temperature	-205/8/2012eg;C to 605/8/2012eg;C (-45/8/2012eg;F to 1405/8/2012eg;F)
Humidity	0~80% RH
<b>Note</b>	Product weights, measurements and connectors indicate a single unit only (either Host or Remote)
Shipping (Package) Weight	3.5 lb [1.6 kg]
Included in Package	1 - Local Unit

Included in Package	1 - Remote Unit
Included in Package	2 - Packs Rubber Feet
Included in Package	2 - Power Adapters
Included in Package	1 - Instruction Manual

**Certifications, Reports and Compatibility**

