

USB VGA Console Extender over CAT5 UTP (500 ft)

StarTech ID: SV565UTPUGB



The SV565UTPUGB USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location
- Control remote machines and security monitoring systems

Features

- USB computers are supported at the host and remote locations (USB keyboard and mouse required for remote console)
- Cables Included for a ready out of the box setup
- Can be used with a single computer or connected to an existing KVM switch
- Easy installation using industry-standard UTP network cable
- Intuitive hotkey commands
- Supports most combo keyboard and mouse sets (including Wireless)
- Supports auto-switching between host and remote users or dedicated control

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	1 - VGA (15 pin; High Density D-Sub) Female
Other Interface(s)	1 - RJ-45 Female
IP Control	No
Maximum Cable Length	500ft(150m)
Supported Resolutions	1280x1024 @ 300ft(100m) 1024x768 @ 500ft(150m)
Color	Black
Enclosure Type	Steel
Product Length	3 in [75 mm]
Product Width	6.1 in [155 mm]
Product Height	0.8 in [20 mm]
Product Weight	10.6 oz [299 g]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	0.2A
Output Voltage	9 DC
Output Current	0.6A
Center Tip Polarity	Positive
Plug Type	M
Operating Temperature	05/15/2012eg;C to 405/15/2012eg;C (325/15/2012eg;F to 1045/15/2012eg;F)
Storage Temperature	-205/15/2012eg;C to 605/15/2012eg;C (-45/15/2012eg;F to 1405/15/2012eg;F)
Humidity	0~80% RH
Note	Product weights, measurements and connectors indicate a single unit only (either Host or Remote)
Shipping (Package) Weight	3.8 lb [1.7 kg]

Included in Package	1 - Host Unit
Included in Package	1 - Remote Unit
Included in Package	2 - 6 ft 2-in-1 USB VGA KVM cables
Included in Package	2 - Packs Rubber Feet
Included in Package	1 - Power Adapter
Included in Package	1 - Manual

Certifications, Reports and Compatibility

