

Remote User Station for Enterprise IP KVM Switch

StarTech ID: SV5CONS



This Remote User Station for Enterprise Series IP KVMs provides system administrator access to StarTech.com Enterprise series KVM solutions (i.e. SV1653DXI) located up to 1000 ft. (300m) away - allowing convenient control of two separate KVM solutions without the need of a complete work station.

Applications

- Allows a remote user to have local access to the KVM and attached servers.
- Control two enterprise series KVMs from one remote location up to 1000ft. away.

Features

- Supports a resolution of up to 1280 x 1024 @75, 1000ft. (300m) away
- LED indicator for KVM identification
- Supports most standard USB keyboards and mice
- Hot-key support
- Compact design, with durable hardened metal casing

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	1
PC Interface	USB
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	2 - RJ-45 Female
IP Control	No
Maximum Cable Length	984 ft [300 m]
Maximum Analog Resolutions	1280 x 1024 @75Hz
Color	Black
Enclosure Type	Aluminum
Product Length	4 in [102 mm]
Product Width	4.4 in [112 mm]
Product Height	0.9 in [24 mm]
Product Weight	6.7 oz [190 g]
LED Indicators	1 - Green – Port Indicator
Power Adapter Included	Yes
Input Voltage	115 AC
Output Voltage	5 DC
Output Current	3A
Center Tip Polarity	Positive
Shipping (Package) Weight	1.5 lb [0.7 kg]
Included in Package	1 - Remote User Station
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Sheet

Certifications, Reports and Compatibility

